

Accessories

Slide Rail



For 1U rackmount chassis

- 26" P/N: 9680009153
- Maximum acceptable load: 25kg
- 1 pair included



For 2U and higher rackmount chassis

- 26" P/N: 9680006905
- Maximum acceptable load: 45kg
- 1 pair included


Industrial Disk Tray/Bay



IPC-DT-5121/ IPC-DT-5121B

Shockproof industrial hard disk drive tray with cooling fan and optional front USB and PS/2 interfaces

- Accepted Device: 1 x 3.5" HDD (only for 9.5mm thickness)
- Cooling Fan: 1 x 4 cm
- Color (Codes): Gray (414U), Black (4C2X)
- Dimensions (W x H x D): 148.5 x 42.6 x 171 mm³



989K008733

A frame to securely fix a 3.5" HDD in a 5.25" drive bay

- Accepted Device: 3.5" HDD x 1



IPC-DT-3120E

Mobile rack for converting a 3.5" drive bay to dual 2.5" SATA HDD/SSD trays

- Accepted Device: 2 x 2.5" SATA HDD/SSD (only for HDD/SSD thickness less than 9.6 mm)
- Dimensions (W x H x D): 101.6 x 25.4 x 139 mm³



989K008734

A frame to securely fix two 2.5" HDDs/SSDs in a 3.5" drive bay

- Accepted Device: 2.5" SATA HDD/SSD x 2 (only for HDD thickness less than 9.6 mm)



9892200013E

Module to convert a 5.25" drive bay to a slim ODD and a 3.5" drive bay

- Accepted Device: 3.5" device x 1, slim ODD x 1



96RACK-5SS-CAGE-CR

Mobile rack for converting one 5.25" drive bay to four 2.5" SAS/SATA HDD/SSD trays

- Accepted Device: 2.5" SAS/SATA HDD/SSD x 4
- Dimension (W x H x D): 146 x 41 x 170 mm³



IPC-DT-5230E

Mobile rack for converting dual 5.25" drive bays to three 3.5" SAS/SATA HDD trays

- Accepted Device: 3.5" SAS/SATA HDD x 3 or 2.5" SAS/SATA HDD/SSD x 3
- Cooling Fan: 1 x 8 cm
- Dimensions (W x H x D): 146.5 x 86 x 225 mm³



96RACK-5-SS-CR-B2

Mobile rack for converting one 5.25" drive bay to one slim ODD and two 2.5" SAS/SATA HDD/SSD trays

- Accepted Device : slim ODD x 1 , 2.5" SAS/SATA HDD/SSD x 2
- Dimension (W x H x D): 146 x 41.3 x 170 mm³

Add-on Card Hold Down Kit



98RKBTO509E

Add-on card hold down kit (short)

- Bracket Q'ty of each kit : 5 pcs
- For PCI add-on card with height 72.3mm ~ 87.3mm and PCIe add-on card with height 81.7mm ~ 91.8mm



98RKBTO510E

Add-on card hold down kit (long)

- Bracket Q'ty of each kit : 5 pcs
- For PCI add-on card with height 54.8mm ~ 75.7mm and PCIe add-on card with height 59.3mm ~ 80.2mm

Accessories

USB Cables



Part Number	1700008461	1700003195	1700002204	1700014398	1700020277-01
Description	USB 2.0 cable with 4 ports	USB 2.0 cable with 2 ports	USB 2.0 cable with 2 ports	USB 2.0 cable with 4 ports	USB 3.0 cable with 2 ports
Cable Length	30.5 cm (12.01")	17.5 cm (6.89")	27 cm (11.92")	30.5 cm (12.01")	30 cm (11.81")
Remark	For ATX/Micro-ATX MB, full-sized SBC			For half-sized SBC	For ATX/Micro-ATX MB, full/half-sized SBC

SATA Cables



Part Number	96CB-SATAPOWER-6P1	1700022749-11	1700019381	1700007351	1700003194
Description	SATA power cable for slim ODD	SATA power cable for HDD/SSD	SATA data cable (right angle)	SATA data cable (right angle)	SATA data cable
Cable Length	10 cm (3.94")	10 cm (3.94")	55 cm (21.65")	40 cm (15.75")	60 cm (23.62")
Remark	Big 4 P to SATA power cable for Slim ODD	Big 4 P to SATA power cable for HDD/SSD	SATA data cable with 1 right angle and 1 vertical connectors	SATA data cable with 1 right angle and 1 vertical connectors	SATA data cable with vertical connectors with locks

COM and Printer Ports Cables



Part Number	1701092300	1701090401	1700020294-01	1700008762
Description	COM cable with 2 ports	COM cable with 1 port	Printer (Parallel) port cable	COM cable with 2 ports
Cable Length	28.5 cm (11.22")	40 cm (15.75")	42.0 cm (16.54")	22.5 cm (8.86")
Remark	For ATX/Micro-ATX MB, full-sized SBC		For ATX/Micro-ATX MB, full-sized SBC	For half-sized SBC

Accessories

Video Cables



Part Number	PCE-DP10-00A1E	1700021831-01	1700008822-11
Description	Display port cable	DP to DVI port cable	DVI to DVI port cable
Cable Length	25 cm (9.84")	30 cm (11.81")	30 cm (11.81")
Remark	Video cable for converting on board DP connector to external DP port supporting DP 1.1a/1.2 signaling	Video cable for converting on board DP connector to external DVI-D port	Video cable for converting on board DVI connector to external DVI-D port

Other Cables



Part Number	1700006915	1700006916	1700024754-01
Description	Cable for ACP-4000MB front LED board	Cable for IPC-610MB-H front LED board	Power cable for GPU card
Cable Length	60 cm (23.62")	60 cm (23.62")	10 cm
Remark	For those Advantech motherboards with VOLT1 connector too far away from the chassis LED board		2*B4P Molex power connector to 6+2P PCIe power cable for GPU card