

UMK-SE 11,25-1 GY - Lateral element



2973957

<https://www.phoenixcontact.com/us/products/2973957>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Side element, 11.25 mm wide, without marker groove

Commercial data

Item number	2973957
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AC13
Product key	ACHDCA
GTIN	4017918245771
Weight per piece (including packing)	5.74 g
Weight per piece (excluding packing)	5.595 g
Customs tariff number	85389099
Country of origin	PL

UMK-SE 11,25-1 GY - Lateral element



2973957


<https://www.phoenixcontact.com/us/products/2973957>

Technical data

Product properties

Product type	Panel mounting base side part
Housing type	Press-drawn section housings
Housing series	UMK
Product family	UMK SE

Dimensions

Dimensional drawing	
Length	11.25 mm

External dimensions

Profile width (external)	77 mm
--------------------------	-------

Internal dimensions

Profile width (internal)	72.2 mm
--------------------------	---------

Material specifications

Color (Housing)	gray (RAL 7042)
Flammability rating according to UL 94	V2
Housing material	PA

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
---------------------------------	--


UMK-SE 11,25-1 GY - Lateral element



2973957

<https://www.phoenixcontact.com/us/products/2973957>

Drawings



UMK-SE 11,25-1 GY - Lateral element

2973957

<https://www.phoenixcontact.com/us/products/2973957>



Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2973957>



UL Recognized

Approval ID: E240868

UMK-SE 11,25-1 GY - Lateral element



2973957

<https://www.phoenixcontact.com/us/products/2973957>

Classifications

ECLASS

ECLASS-13.0	27190602
ECLASS-15.0	27190602

ETIM

ETIM 9.0	EC002779
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

UMK-SE 11,25-1 GY - Lateral element



2973957

<https://www.phoenixcontact.com/us/products/2973957>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com