

Part Number : [191930155](#)

Product Description : VersaKrimp Ring Tongue Terminal for 8 AWG Wire, Closed-Brazed Barrel, Stud Size 1/4" (M6), Mylar Tape Carrier

Series Number : 19193

Status : Active

Product Category : Ring and Spade Terminals

Engineering Part Number : D-350-14T



Documents and Resources

Drawings

[191930155 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)


[Creo](#)

Specifications

[PS-19902-015-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)6375-DC (05 Nov 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19193
Description	VersaKrimp Ring Tongue Terminal for 8 AWG Wire, Closed-Brazed Barrel, Stud Size 1/4" (M6), Mylar Tape Carrier
Keyword	Ring Terminal, Ring Terminals
Product Name	VersaKrimp
Style	Ring
Type	Ring Terminal, Metric Ring Terminal
UPC	800753039506

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed - Brazed
Insulation	None
Material - Plating Mating	Tin
Net Weight	2.931/g
Packaging Type	Adhesive Tape on Reel

Stud Size	1/4" (M6)
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	7.19mm max.
Wire Size (AWG)	8
Wire Size mm ²	8.36

Application Tooling

Global

Description	Part Number
ATP Crimp Dies for VersaKrimp High Temperature Nickel Plated Steel Terminals on Tape, 8 AWG	<u>190270105</u>
ATP Crimp Dies for VersaKrimp Copper Ring Tongue Terminals And Butt Splices on Tape, 8 AWG	<u>190270111</u>
ATP Crimp Dies for VersaKrimp Ring Tongue Terminals, for Solid Copper or Steel Wire (Anti Rotation)	<u>190270117</u>
ATP Crimp Dies for Versakrimp 8 AWG Ring Tongue Terminals, for Stripped Magnet or Steel 6 AWG Wire	<u>190270120</u>
ATP Crimp Dies for VersaKrimp Copper Ring Tongue Terminals and Butt Splices on Tape, 8 AWG, use with Tape Crimp Module and ATP-201 Press	<u>190472000</u>

This document was generated on Dec 29, 2025