




Part Number : 2214424241

Product Description : Mini-Fit TPA2/Sigma Female Low Mating Force Crimp Terminal, Copper Alloy, Post-Plated Tin (Sn), 20-18 AWG, 2.10-2.85mm Insulation Diameter, Reel



Series Number : 221442

Status : Active

Product Category : Crimp Terminals

Documents & Resources

Drawings

[2214424241_sd.pdf](#)

[2214420000-PK-000.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[2131370000-PS-000.pdf](#)

[1727180001-TS-000.pdf](#)

[2131370001-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	ⓘ per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	221442
Description	Mini-Fit TPA2/Sigma Female Low Mating Force Crimp Terminal, Copper Alloy, Post-Plated Tin (Sn), 20-18 AWG, 2.10-2.85mm Insulation Diameter, Reel
Application	Power, Wire-to-Wire, Wire-to-Board
Product Name	Mini-Fit Sigma,Mini-Fit TPA2
UPC	198282439226

Electrical

Current - Maximum per Contact	10.0A
Voltage - Maximum	600V AC/DC

Physical

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Copper Alloy
Material - Plating Mating	Tin

Material - Plating Termination	Tin
Net Weight	0.184/g
Packaging Type	Reel
Plating min - Mating	1.250µm
Plating min - Termination	2.500µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	2.10-2.85mm
Wire Size (AWG)	18, 20
Wire Size mm ²	N/A

Mates With / Use With

Use with Part(s)

Description	Part Number
Mini-Fit TPA2 and Mini-Fit Sigma Dual Row Receptacle Housings	<u>172708</u>
Mini-Fit TPA2 and Mini-Fit Sigma Single Row Receptacle Housings	<u>200453</u>

Application Tooling

Global

Description	Part Number
FineAdjust Applicator for Mini-Fit TPA2 Crimp Terminals, 0.50mm ² , 0.75mm ² and 20-18 AWG wires	<u>639036800</u>
Hand Crimp Tool for Mini-Fit TPA2 Male and Female Crimp Terminals, 20 AWG, Large and Small Insulation Grips	<u>2002182100</u>
Hand Crimp Tool for Mini-Fit TPA2 Male and Female Crimp Terminals, 18 AWG, Large and Small Insulation Grips	<u>2002180100</u>

This document was generated on Sep 11, 2025