JB22-10

TE Connectivity has acquired the DIN Rail Terminal Block product range from ABB

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories → Jumper Bars

General Information

Extended Product Type:	JB22-10
Product ID:	1SNK922310R0000
EAN:	3472599163638
Catalog Description:	JB22-10 Jumper Bar
Long Description:	Screw jumper bars

Ordering

Minimum Order Quantity:	5 piece
Customs Tariff Number:	85369010

Popular Downloads

Data Sheet, Technical Information:	1SNK160033D0201
Instructions and Manuals:	1SNK160027C0201

Dimensions

Product Net Width:	22 mm
Product Net Height:	211 mm
Product Net Length:	20.7 mm
Product Net Depth / Length:	20.7 mm
Product Net Weight:	157.4 g

Technical

Spacing:	22 mm
Function:	Jumper Bars
Rated Current (I_n):	Main Circuit 192 A
Rated Short-time Withstand Current (I_{cw}):	for 1 s 8400 A
Rated Voltage (U_r):	1000 V
Rated Impulse Withstand Voltage (U_{imp}):	8000 V
Dielectric Test Voltage:	2200 V
Power Loss:	6.1 W
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	Polyamide

Downloaded from Arrow.com.

Recommended Screw Driver:	4 mm
Suitable For:	D70/22 ZS70

Technical UL/CSA

Maximum Operating Voltage UL/CSA:	Main Circuit 600 V

Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment

Certificates and Declarations (Document Number)

ATEX Certificate:	1SND162004A1708
CB Certificate:	1SND161034A0202
Instructions and Manuals:	1SNK160027C0201
RoHS Information:	1SND230499F0202

Classifications

Object Classification Code:	X
E-nummer:	2925396
ETIM 4:	EC000489 - Cross-connector for terminal block
ETIM 5:	EC000489 - Cross-connector for terminal block
ETIM 6:	EC000489 - Cross-connector for terminal block

Container Information

Package Level 1 Units:	5 piece
Package Level 1 Width:	54 mm
Package Level 1 Depth / Length:	252 mm
Package Level 1 Height:	52 mm
Package Level 1 Gross Weight:	0.787 kg
Package Level 1 EAN:	3472599163638
Package Level 2 Units:	45 piece
Package Level 2 Width:	200 mm
Package Level 2 Depth / Length:	300 mm
Package Level 2 Height:	200 mm
Package Level 2 Gross Weight:	7.36 kg
Package Level 3 Units:	4320 piece
Product Packing Type:	Box

Downloaded from Arrow.com.



Downloaded from Arrow.com.