

Specification Sheet

Part Number: 133-02868

HellermannTyton connector clips provide a simple and easy method for mounting connectors to a mounting surface in a variety of applications.

Engineered design options include anti-rattle disc, anti-rotation oval fir tree and clamp for mounting on edges. HellermannTyton offers an assortment of connector clips available for a variety of connector slot designs found on most of the largest global connector manufacturers.



Connector Clip with Fir Tree, 1.8 - 7.3 mm Panel Thickness, 6.2 - 6.5 mm Hole Dia, PP, Black, 2000/ctn

Article Number	133-02868
Type	CCFT6.35HTS6.25
Color	Black (BK)
Quantity Per	carton
Product Description	Connector Clips feature various attachment point configurations to accommodate the many connectors on the market. They are first mated with a connector on a wire harness or cable assembly, then secured to a surface using the integrated mount. With so many configurations available, attachment surfaces can be a hole, edge, stud or even another harness assembly.
Short Description	Connector Clip with Fir Tree, 1.8 - 7.3 mm Panel Thickness, 6.2 - 6.5 mm Hole Dia, PP, Black, 2000/ctn

Global Part Name	CCFT6.35HTS6.25-PP-BK
Length L (Imperial)	0.98
Length L (Metric)	25.0
Fixation Method	Fir Tree
Width W (Imperial)	0.76
Width W (Metric)	19.3
Height H (Imperial)	0.78
Height H (Metric)	19.76
Panel Thickness Min (Imperial)	0.07
Panel Thickness Max (Imperial)	0.21
Panel Thickness Min (Metric)	1.8
Panel Thickness Max (Metric)	7.3
Mounting Hole Diameter D (Imperial)	0.25 "
Mounting Hole Diameter D (Metric)	6.35 mm (hexagonal) 6.5 mm
Mounting Hole Diameter D Min (Imperial)	0.24
Mounting Hole Diameter D Max (Imperial)	0.26

Mounting Hole Diameter D Max (Metric) 6.5

Material Polypropylene (PP)

Material Shortcut PP

UV Resistant (Yes/No) Yes

Use Conditions For Indoor Use Only

Operating Temperature -40°F to +239°F (-40°C to +115°C)

Reach Compliant (Article 33) Yes

ROHS Compliant Yes

Package Quantity (Imperial) 2000

Package Quantity (Metric) 2000

Customs Number 3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
Contact Us RoHS/WEEE Compliance Disclaimer Terms and Conditions