

Active

PRODUCT DRAWING
English

3D PDF

See All Documentation

TE CONNECTIVITY (TE)

024 HOUSING FFC PIN DR 100CL

FFC | FFC

1-88190-0
TE Internal Number: 1-88190-0

Always EU RoHS/ELV Compliant

Connector Type **Housing**

Connector Style **Plug**

Centerline **2.54 mm [.1 in]**

Number of Positions **24**

Number of Rows **2**

See All Features

Feedback

North America

GET SAMPLE

SAVE TO LIST

Contact us to request pricing, availability and customization options.

© 2016 TE Connectivity Ltd. family of companies. All Rights Reserved

PDF (TIFF AVAILABLE)
English

CAD Files

Customer View Model
2D_DXF.ZIP
English

Customer View Model
3D_IGS.ZIP
English

Customer View Model
3D_STP.ZIP
English

3D PDF
PDF
English

Product Specifications

Product Specification: Connector, Flexible Flat Conductor Cable, .100 Inch Centerline
PDF
English

Application Specification: Flexible Flat Cable (FFC) Housings With Contact Cavities On 2.54-mm (.100-in.) Centerline Spacing
PDF
English

Instruction Sheets

Instruction Sheet (U.S.): Extraction Tools 91047-[ ]
PDF
English

Extraction Tool For Flexible Flat Cable (FFC)
PDF
English

Extraction Tool For Flexible Flat Cable (FFC)
TIF
English

COMPATIBLE

Products - 23 Results

View All | Compare 0/10

Relation Type

RELATIONSHIP
Contacts
Identifies Contacts compatible with a given Housing

See All Contacts



PRODUCT - CONTACTS

Connectors - FFC Contacts
FFC | FFC

FFC, PIN CONTACT, LP, ROUND WIRE, - 494034-2

TE INTERNAL NUMBER: 494034-2

Active

Always EU RoHS/ELV Compliant

Centerline **2.54 mm**

Wire/Cable Type **Round Wire, Discrete**

Contact Type **Pin**

Contact Mating Area Plating Material **Gold**

Packaging Method **Bag**

Quick View

RELATIONSHIP
Contacts
Identifies Contacts compatible with a given Housing

See All Contacts



PRODUCT - CONTACTS

Connectors - FFC Contacts
FFC | FFC

FFC PIN CONT 15AU RL - 88117-3

TE INTERNAL NUMBER: 88117-3

Active

Not EU RoHS or ELV Compliant

Centerline **2.54 mm**

Wire/Cable Type **FFC**

Contact Type **Pin**

Contact Mating Area Plating Material **Gold Flash/Palladium Nickel or Gold/Nickel**

Packaging Method **Reel**

Quick View

RELATIONSHIP
Contacts
Identifies Contacts compatible with a given Housing

See All Contacts



PRODUCT - CONTACTS

Connectors - FFC Contacts
FFC | FFC

FFC PIN ROUND WIRE PLATED - 86557-6

TE INTERNAL NUMBER: 86557-6
ALIAS ID: 010-5627-00

Active

Always EU RoHS/ELV Compliant

Centerline **2.54 mm**

Wire/Cable Type **Round Wire, Discrete**

Contact Type **Pin**

Contact Mating Area Plating Material **Gold**

Packaging Method **Reel**

Quick View

Downloaded from Arrow.com.