


© 2022 TE Connectivity. All Rights Reserved.


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	07APR2022	N.H	L.C
	B	REVISED PER ECR-24-206382	29SEP2024	N.H	L.C
	B1	REVISED PER ECR-25-248407	26JUL2025	N.H	J.H


5 POSITION SHOWN











1. MATERIAL: PBT, COLOR: SEE TABLE
2. RECOMMENDED MATING PART: X-2382946-X
3. PACKAGING: LOOSE PIECE

DIM B	DIM A	COLOR	DESCRIPTION	TCPN
			PRODUCT	
1.5	5.36	BLACK	SGI 1.50, TPA, 2 POS, BLACK	2383410-2
3.0	6.86		SGI 1.50, TPA, 3 POS, BLACK	2383410-3
4.5	8.36		SGI 1.50, TPA, 4 POS, BLACK	2383410-4
6.0	9.86		SGI 1.50, TPA, 5 POS, BLACK	2383410-5
7.5	11.36		SGI 1.50, TPA, 6 POS, BLACK	2383410-6
9.0	12.86		SGI 1.50, TPA, 7 POS, BLACK	2383410-7
10.5	14.36		SGI 1.50, TPA, 8 POS, BLACK	2383410-8
12.0	15.86		SGI 1.50, TPA, 9 POS, BLACK	2383410-9
13.5	17.36		SGI 1.50, TPA, 10 POS, BLACK	1-2383410-0
15.0	18.86		SGI 1.50, TPA, 11 POS, BLACK	1-2383410-1
16.5	20.36		SGI 1.50, TPA, 12 POS, BLACK	1-2383410-2
1.5	5.36	NATURAL	SGI 1.50, TPA, 2 POS, NATURAL	2-2383410-2
3.0	6.86		SGI 1.50, TPA, 3 POS, NATURAL	2-2383410-3
4.5	8.36		SGI 1.50, TPA, 4 POS, NATURAL	2-2383410-4
6.0	9.86		SGI 1.50, TPA, 5 POS, NATURAL	2-2383410-5
7.5	11.36		SGI 1.50, TPA, 6 POS, NATURAL	2-2383410-6
9.0	12.86		SGI 1.50, TPA, 7 POS, NATURAL	2-2383410-7
10.5	14.36		SGI 1.50, TPA, 8 POS, NATURAL	2-2383410-8
12.0	15.86		SGI 1.50, TPA, 9 POS, NATURAL	2-2383410-9
13.5	17.36		SGI 1.50, TPA, 10 POS, NATURAL	3-2383410-0
15.0	18.86		SGI 1.50, TPA, 11 POS, NATURAL	3-2383410-1
16.5	20.36		SGI 1.50, TPA, 12 POS, NATURAL	3-2383410-2

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±0.30
2 PLC ±0.15
3 PLC ±-
4 PLC ±-
ANGLES ±-

MATERIAL: SEE NOTE -
FINISH: -

DWN: LEO CHEN 17DEC2020
CHK: DANIEL ZHANG 17DEC2020
APVD: DANIEL ZHANG 17DEC2020
PRODUCT SPEC: 108-106451
APPLICATION SPEC: 114-106497
WEIGHT: -

CUSTOMER DRAWING

TE Connectivity

NAME: TPA, SGI 1.50
-

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-2383410	-


SCALE 15:1 | SHEET 1 OF 2 | REV B1

Downloaded from Arrow.com.


© 2022 TE Connectivity. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			


2 POSITION




3 POSITION




4 POSITION




5 POSITION




6 POSITION




7 POSITION




8 POSITION




9 POSITION




10 POSITION



11 POSITION



12 POSITION



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±-
1 PLC	±0.30
2 PLC	±0.15
3 PLC	±-
4 PLC	±-
ANGLES	±-

MATERIAL: SEE NOTE -

FINISH: - -

DWN	LEO CHEN 17DEC2020
CHK	DANIEL ZHANG 17DEC2020
APVD	DANIEL ZHANG 17DEC2020
PRODUCT SPEC	108-106451
APPLICATION SPEC	114-106497
WEIGHT	-

TE Connectivity

NAME: TPA, SGI 1.50 -

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-2383410	-

CUSTOMER DRAWING | SCALE 15:1 | SHEET 2 OF 2 | REV B1

Downloaded from Arrow.com.