

BMP®61 Labeling System,
BradyPrinter™ M611

Ribbon Series:

R6600

Part Number:

M61-R6610

ADD TO CART

1



Add To Favorites

People Also
Viewed



Overview

BMP®61 Series ribbon cartridges allow users to change ribbons in seconds.

- One-color ribbon for printing a single color onto a label
- R6600 Series Resin Formulation offers excellent solvent and friction resistance when printed on the appropriate label material from Brady®
- Recommended for printing on heat shrinkable tubing materials from Brady®, including material numbers

- Automatic label formatting with smart cell technology and easy loading

Specifications

Country of Origin	MX - All trade information (i.e. Country of Origin, Harmonized Schedule code, and/or Export Control Classification Number) and related assistance provided by Brady Corporation and its affiliates is provided for informational purposes only and is subject to change without notice. Any use of such information by you is without recourse to Brady Corporation or its affiliates and is at your own risk. This information is not provided as legal advice or as a substitute for obtaining specific legal advice. If you have any questions regarding your specific situation, you should consult your attorney.
Catalog Page #	354
UOM	Roll of 75 Feet
Product Number	148134
UPC	754473580568
Ribbon Color Options	Single Color Ribbon
Ribbon Formulation Type	Resin
Ribbon Roll Type	Ribbon in Cartridge
Ribbon Series	R6600
Ribbon Size	2 in W x 75 ft L
Ribbon Width	2 in
Roll Length	75 ft
Trade Name	BMP®61
UNSPSC	45101711
Color	Black
For Use with Printer	BMP®61 Labeling System, BradyPrinter™ M611
Label/Media Format	Ribbon in Printer Specific Cartridge
Resistance Properties	Solvent-Resistant

Solutions

[Floor Marking Guide](#)

Services

[Lockout Tagout Services](#)

Help

[Contact Us](#)

Resources

[Find a Distributor](#)

GHS Label Compliance
Lockout Tagout Compliance
Arc Flash Labeling Requirements
Cable and Wire Label Options
Product and Barcode Labeling

Arc Flash Services
Confined Space Services
Software Programming & Integration
Label Template & File Conversion
Printer Use & Training
Printer Preventative Maintenance
Toll and Custom Coating
Authentication & Tracking Services

Website Feedback
Knowledge Center
Printer Drivers & Firmware
Brady Software Updates
Safety Data Sheets
Technical Data Sheets
WEEE-RoHS Compliance
Product Certification
Printer Registration


Design Custom Safety Signs
Create Custom THT Labels
Printer Selection Tool
Label Selection Tool
Digital Catalog
Request a Catalog
Interactive Facility Map
EPA e-Manifest Update

Corporate **Other BradyContact Sites**

[About](#)
[Careers](#)
[Investors](#)
[Privacy Policy](#)
[Terms and Conditions](#)
[Terms of Use](#)
[ISO Certificates](#)
[Distributor Portal](#)
[International Sites](#)
[Safety Services & Software](#)
[Brand Protection Solutions](#)

6555 W. Good Hope Rd.
Milwaukee, WI 53223
Phone: 888-250-3082
Hours: 7am-6pm CT
Monday - Thursday;
Friday 7am-5pm CT

Brady (NYSE:BRC) is a manufacturer of complete solutions that identify and protect people, products and places. Brady's products help customers increase safety, security, productivity and performance and include high-performance labels, signs, safety devices, printing systems and software.



2019 © Brady Worldwide, Inc.