


This document is the property of Amphenol Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior concert, & that no right is granted to disclose or to use any information in this document.

REVISIONS				
SYM	ECN	DESCRIPTION	DATE	APPROVED
1	HK--	First Release Drawing	06/12/08	IP







RECOMMENDED P.C.B LAYOUT

(TOLERANCE +/-0.05)

Customer Drawing

D-SUB TECHNICAL DATA

SHELL :	Steel,100u" min tin over 50u" min nickel
BODY :	Glass filled thermoplastic. Flame retardant to UL94 V-0, Color Black
CONTACTS :	Copper alloy Gold flash over 1.25um(50u") min nickel on mating area
BOARDLOCK :	Brass. 100u" min tin over 50u" min nickel
REAR INSERT :	Brass. 100u" min tin over 50u" min nickel
GROUNDING :	Grounding strap : Brass. 100u" min tin over 50u" min nickel
ELECTRICAL :	Voltage rating 300 V Rms to 50 Hz Current rating 3A Withstanding Voltage >1000 V Rms to 50 Hz for one minute Insulation resistance >5000 M Ohms Contact resistance 20 mOhms max.
CLIMATIC :	Temperature range 85°C, peak at +125°C Damp heat 56 days(40°C-95% HR)
MARKING :	Amphenol-...(Series No.) Commercial reference Manufacturing date

PRODUCT CODE

L 17 SM2 XX S B 1 1 X

- RoHS Compliance
- Configuration: 09,15,25
- Contact type: S:Socket
- Boardlocks/grounding tab: B=V2 grounding tab +LIF boardlocks (PCB=1.6)
- Packaging: R=reel T=tube
- Contact plating: 1=gold flash
- Mounting options: 1=Rear insert 4-40

DIM.S / SHELL	A	B	C	D	E	PITCH	F	K
E	31.15	16.40	25.00	8.03	12.40	2.74	10.97	16.30
A	39.40	24.80	33.30	8.03	12.40	2.74	19.20	24.60
B	53.30	38.50	47.70	8.03	12.40	2.76	33.12	38.30

UNLESS OTHERWISE SPECIFIED TOLERANCES

U.S.	METRIC
.X +/-	0.50
.XX +/-	0.30
.XXX +/-	0.20
FRACTIONS +/-	
ANGLES +/-	2°

FOR MATERIALS AND FINISHES SEE NOTES

REMOVE SHARP EDGES

DIMENSIONS

U.S.	INCHES
METRIC	MM

APPROVAL	DATE
DRAWN Christina.cui	06/12/08
CHECKED Lik.wang	06/12/08
CHECKED	
DRAWING FILE :	

ANGLE OF PROJECTION

Amphenol

Amphenol East Asia Limited

TITLE: Surface mount connectors SM2 Series

SIZE	DRAWING NO.	REV.
A4	C L17SM2XXSB11X	1

SCALE NONE SHEET 1 OF 1

Downloaded from Arrow.com.