

# Specifications



## Eaton 170M1366

Eaton Bussmann series high speed square body fuse, 80 A, 690 V (IEC), 700 V (UL), Size 0, Top fuse status indicator

### General specifications

<b>PRODUCT NAME</b>	Eaton Bussmann series high speed square body fuse
<b>CATALOG NUMBER</b>	170M1366
<b>MODEL CODE</b>	FUSE 80A 690V 000/80 AR UC
<b>UPC</b>	051712216678
<b>EAN</b>	5027590440837
<b>PRODUCT LENGTH/DEPTH</b>	105 mm
<b>PRODUCT HEIGHT</b>	46 mm
<b>PRODUCT WIDTH</b>	300 mm
<b>PRODUCT WEIGHT</b>	134 g
<b>COMPLIANCES</b>	RoHS Compliant CE Marked
<b>CERTIFICATIONS</b>	IEC Rated UL Recognized
<b>GLOBAL CATALOG</b>	170M1366

## Product specifications

<b>AMPERAGE RATING</b>	80 A
<b>BREAKING CAPACITY</b>	200 kA
<b>FUSE INDICATOR</b>	Top fuse status indicator
<b>INSULATED METAL GRIPPING LUGS (IMGL)</b>	No
<b>UTILIZATION CATEGORY</b>	aR (accompanied semiconductor protection)
<b>VOLTAGE TYPE</b>	AC
<b>FUSE SIZE</b>	000
<b>RATED VOLTAGE AC</b>	690 V
<b>CURRENT TYPE</b>	AC
<b>CLASS</b>	Class aR
<b>CLEARING (I<sub>2</sub>T)</b>	2550 at 660 V
<b>WATT LOSSES</b>	19 W
<b>FUSE SHAPE</b>	Square body, slotted offset bolted tags
<b>PRE ARC (I<sub>2</sub>T)</b>	380
<b>COLOR</b>	None
<b>INTERRUPT RATING</b>	200 kAIC
<b>CONNECTION</b>	Blade end x blade end
<b>CONSTRUCTION SIZE</b>	Other
<b>VOLTAGE RATING</b>	690 V (IEC), 700 V (UL)
<b>TYPE</b>	Fuse
<b>APPLICATION</b>	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
<b>FUSE TYPE</b>	DIN 43653 /80 Visual indicator

## Resources

### CATALOGS

[eaton-bussmann-series-iec-high-speed-fuses-catalogue-ca135001en-english.pdf](#)

[Bussmann series complete full line catalog no. 1007](#)

[170M1366~Eaton Bussmann series high speed square body fuse](#)

### DECLARATIONS OF CONFORMITY

[eaton-high-speed-square-body-fuse-declaration-of-conformity-eu250049en.pdf](#)

[eaton-high-speed-square-body-fuse-declaration-of-conformity-uk250927en.pdf](#)

### DRAWINGS

[eaton-fuses-fuse-link-dimensions-005.eps](#)

### MANUALS AND USER GUIDES

[High speed fuses application guide](#)

### MCAD MODEL

[eaton-hs-square-body-fuses-mcad-3d-models-170m1366.stp](#)

### PRODUCT NOTIFICATIONS

[eaton-bussmann-series-170m-fuses-product-change-notice-pcn-bur-00193-en-us.pdf](#)

[eaton-bussmann-series-ukca-marking-high-speed-fuses-pcn-bur-00167-en-gb.pdf](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

