












結線部形状
Wrapping Part Form

表2．
Table2.


製　番 Part No.	めっき Plating
MR-( )MW	銀めっき Silver Plating
MR-( )MWG	金めっき Gold Plating

表3．
Table3.

製　番 Part No.	絶縁体　Insulator	
	材質 Material	備考 Note
MR-8MW (G)	ジアリルフタレート Diallyl phthalate	青色 Blue
MR-16MW (G)	PBT樹脂 PBT (GF)	青色、 UL94V-0
MR-20MW (G)		
MR-25MW (G)		
MR-34MW (G)		Blue、 UL94V-0
MR-50MW (G)		



端子番号詳細は別紙参照のこと。
See an attached sheet for terminal No. details.



パネル取付穴参考寸法図
Recommended Size of Mounting Holes

注1．当図はMR-25MW (G) を示しています。
注2．適合ケーブル　Ø0.32~Ø0.4

Note1.This figure shows MR-25MW (G).
Note2.Applicable Cable:Ø0.32~Ø0.4

表1．
Table1.

製　番 Part No.	n	n_1	n_2	A±0.3	B±0.15	C±0.3	D±0.2	E	F	G	X±0.1
MR-8MW (G)	8	2	1	22.4	17.4	11.9	10	5.2	1.3	2.6	12.4
MR-16MW (G)	16	5	3	30.2	25.2	19.7		13.0	5.2	7.8	20.2
MR-20MW (G)	20	6	5	32.8	27.8	22.3		15.6	6.5	13.0	22.8
MR-25MW (G)	25	8	6	38.0	33.0	27.5	9.6	20.8	9.1	15.6	28.0
MR-34MW (G)	34	11	9	45.8	40.8	35.3		28.6	13.0	23.4	35.8
MR-50MW (G)	50	17	13	61.4	56.4	50.9		44.2	18.2	33.8	51.4

HONDA
PRINT RM
OCT.16.2003
ISSUED

改版 LTR.	年月日 DATE	変更者 BY	変更内容 REV.DESCRIPT
3			
2			
1	031014	M.Miyazaki	Reshape

番号 No.	部品名称 PART NAME	材質 MATERIAL	個数 QTY	処理 FINISH	備考 NOTE
2	雄コンタクト Contact	りん青銅 Phosphorbronze	n	表2．参照 See Table2.	———
1	雄絶縁体 Insulator	表3．参照 See Table3.	1	——— ———	表3．参照 See Table3.

年月日 DATE	尺度 SCALE	単位 UNIT	3角法
02.19 Feb.19(1972)	2/1	mm (INCH)	3RD. A. P

製図 DR.	設計 DE.	検図 CHK.	検図 CHK.	承認 APP.
M.MIYAZAKI	M.MIYAZAKI	S.IIJIMA	C.NUNOKAWA	H.EBIHARA

本多通信工業株式会社
HONDA TSUSHIN KOGYO CO., LTD.

名称 NAME	MR形雄コネクタ（ラッピングタイプ） MR Series Male Connectors(Wrapping type)	
製番 PART NO.	MR-(8~50)MW (G)	REV. 1A

ID= MR-@MW@ BA

HONDA TSUSHIN KOGYO CO., LTD.
The product information in this data is for reference only.
This is subject to change without notice.
Contact our sales staff before ordering or
please request the most current information.
Drawings are the most accurate design information.
Downloaded from Arrow.com.