



359 SERIES Indicator Base

MECHANICAL / SPECIFICATIONS

BASE PART NUMBER:

[359-8430-09-502](#)

MOUNTING:

15/32" clearance hole (.468")

MOUNTING ORIENTATION:

Front

BULB BASE SIZE:

T-1 3/4 Midget Flange

TERMINATION:

Brass solder terminals, hot tinned
with elongated slots

HOUSING FINISH:

Aluminum housing, black anodized finish

HARDWARE:

Internal-tooth lock washer and mounting nut:
Steel, cadmium plated with yellow iridescent
chromate finish

VOLTAGE / RESISTOR: Bulb Dependent

LENS CAP OPTIONS:

Stovepipe and Cylindrical
Non-Diffused and Translucent

MILITARY COMPLIANT: Yes

MILITARY CROSS #: LH73/1

CERTIFICATIONS & RATINGS

RoHS Compliant w/6C exemption


FEATURES & BENEFITS

- Two terminals – fully insulated
- For mounting in 15/32" clearance hole
- Meet or exceed environmental and operational requirements of MIL-L-6723 and MIL-L-3661C
- Anti-rotation (locked) construction: provides for secure locking of the socket terminal assembly in the mounting bushing and of the center terminal to the insulating disc. The notched mounting bushing receives the matched insulating disc to prevent the rotation of the mounting bushing.

APPLICATION

Aircraft instrumentation, ground vehicles, shipboard systems, communication equipment, power distribution, radar and sonar systems, control panels, safety systems

DIMENSIONS inches [mm]




MAX PANEL THICKNESS 3/16"


RECOMMENDED PANEL CUTOUT

Base, bulb, and cap are required for a complete indicator assembly and need to be purchased separately.

ORDERING INFORMATION



STOVEPIPE LENS CAP



CYLINDRICAL LENS CAP

STOVEPIPE LENS CAP Non-Diffused

	Type Designation	Part Number	Lens Cap Color
	LC12RN2	162-0931	● Red
	LC12GN2	162-0932	● Green
	LC12YN2	162-0933	● Yellow
	LC12BN2	162-0934	● Blue
	LC12CN2	162-0937	○ Clear

Translucent

	Type Designation	Part Number	Lens Cap Color
	LC12RT2	162-0971	● Red
	LC12GT2	162-0972	● Green
	LC12YT2	162-0973	● Yellow
	LC12BT2	162-0974	● Blue
	LC12WT2	162-0975	○ White


CYLINDRICAL LENS CAP Non-Diffused

	Type Designation	Part Number	Lens Cap Color
	LC29GN2	162-1432	● Green
	LC29YN2	162-1433	● Yellow
	LC29CN2	162-1437	○ Clear

Translucent

	Type Designation	Part Number	Lens Cap Color
	LC29RT2	162-1471	● Red
	LC29GT2	162-1472	● Green
	LC29YT2	162-1473	● Yellow
	LC29BT2	162-1474	● Blue
	LC29WT2	162-1475	○ White

ORDERING INFORMATION



FLAT LENS CAP

FLAT LENS CAP

Non-Diffused

	Type Designation	Part Number	Lens Cap Color
	LC11RN2	178-0331-500	● Red
	LC11GN2	178-0332-500	● Green
	LC11YN2	178-0333-500	● Yellow
	LC11BN2	178-0334-500	● Blue
	LC11CN2	178-0337-500	○ Clear

Translucent

	Type Designation	Part Number	Lens Cap Color
	LC11RT2	178-0371-500	● Red
	LC11GT2	178-0372-500	● Green
	LC11YT2	178-0373-500	● Yellow
	LC11BT2	178-0374-500	● Blue
	LC11WT2	178-0375-500	○ White