YAZ264TCG1, Compression Terminal, 2/0 AWG Cu, 125 Navy, 4-Hole, 1/4" Stud, Split Pad, Long Barrel



By Burndy
Catalog # YAZ264TCG1

HYLUG™ Copper Compression Terminal; Split Pad, 4 Holes,W/Insp Window, 2/0 AWG Code, 125 Navy, Black, 13 Index, 1/4 IN Bolt Size, 1-9/16 IN Strip Length

Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Material	COPPER
Conductor - Copper Str Size	2/0 AWG
Conductor - Copper DLO Size Range	N/A
Conductor Size	2/0 AWG
Conductor Type	CODE
Conductor - Copper Str Size Range	2/0 AWG

Configuration

Number of Pad Holes	4
Connector Type	LONG BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	1.38 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/4
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	94 mm
Dimension - Hole Size mm	6.9 mm
Dimension - Hole Size inch	0.27
Dimension - Strip Length inch	1-9/16
Dimension - Stud Size inch	1/4
Dimension - Stud Size fraction	1/4
Dimension - Bolt Size fraction	1/4
Physical Attribute - Tongue Angle	Straight
Dimension - B Length inch	1.50 in
Dimension - Bolt Size inch	0.25
Dimension - Length Overall inch	3.71 in

General

Trade Name	HYLUG™
Die Index	13
Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Plated	Y
Color Code	Black
UPC	781810636077
Type	Standard Barrel, Tin Plated
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810636077
UPC 14 Digit GTIN	00781810636077

Logistics

Minimum Pack Quantity	1
Pallet Quantity	7680
Carton Quantity	20

Operational

Temperature Rating	194

Downloaded from Arrow.com.

Product Assets

Catalog [English]

© 2026 Hubbell Incorporated. All rights reserved

Downloaded from Arrow.com.