

# CES-B16-WRG-BK - Flat gasket



0801726

<https://www.phoenixcontact.com/us/products/0801726>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Flat gasket made of NBR, size B16



## Commercial data

Item number	0801726
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	BF67
Product key	AF7CZX
GTIN	4046356675253
Weight per piece (including packing)	11.33 g
Weight per piece (excluding packing)	2.91 g
Customs tariff number	40169300
Country of origin	DE

# CES-B16-WRG-BK - Flat gasket

0801726

<https://www.phoenixcontact.com/us/products/0801726>



## Technical data

### Product properties

Product type	Seal
Type	B16

### Dimensions

Dimensional drawing	
Width	57.5 mm
Height	2.5 mm
Length	120 mm
Drill hole distance, horizontal	103 mm
Drill hole distance, vertical	32 mm
Hole diameter	4.5 mm

### Material specifications

Seal material	NBR
---------------	-----

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-20 °C ... 80 °C (static)
---------------------------------	---------------------------

# CES-B16-WRG-BK - Flat gasket


0801726

<https://www.phoenixcontact.com/us/products/0801726>



## Drawings

Dimensional drawing



Dimensional drawing

# CES-B16-WRG-BK - Flat gasket

0801726

<https://www.phoenixcontact.com/us/products/0801726>



## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/0801726>

### DNV

Approval ID: TAE00003VJ

# CES-B16-WRG-BK - Flat gasket



0801726

<https://www.phoenixcontact.com/us/products/0801726>

## Classifications

### ECLASS

ECLASS-13.0	23071590
ECLASS-15.0	23071590

### ETIM

ETIM 9.0	EC002498
----------	----------

### UNSPSC

UNSPSC 21.0	31401600
-------------	----------

# CES-B16-WRG-BK - Flat gasket



0801726  
<https://www.phoenixcontact.com/us/products/0801726>

## Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.0 Climate Change	
CO2e kg	0.463 kg CO2e

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)