



Part Number : [640160133](#)

Product Description : ServiceGrade Hand Crimp
Tool for MX150 Crimp Terminals, 22-14 AWG

Series Number : 207129

Status : Active

Product Category : Crimp Presses and Crimp Hand
Tools



Documents & Resources

Tooling Specifications

[ATS-640160133-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per ED/30/2017 (7 July 2017)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Part Details

General

Status	Active
Category	Crimp Presses and Crimp Hand Tools
Series	207129
Description	ServiceGrade Hand Crimp Tool for MX150 Crimp Terminals, 22-14 AWG
Comments	ServiceGrade crimp hand tools are low cost ratcheting hand tools used in field repair for a limited number of terminations. If a high quality tool is required or a higher volume of terminations required, please purchase the corresponding PremiumGrade crimp hand tool. A ServiceGrade crimp tool may or may not have a terminal locator and in some case may need the locator removed to operate properly; Type: SERV GRADE
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	toolingsupport@molex.com
Product Name	MX150,ServiceGrade
Tool Type	Hand Crimp Tool
UPC	800756819716
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific

	<p>connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer.</p> <p>Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.</p>
--	---

Applicable Parts

Description	Part Number
MX150 Female Terminal for Mat-Sealed Connectors, Gold Plating, 16-14 AWG, Right Reel Payoff	<u>330012003</u>
MX150 Female Terminal for Mat-Sealed Connectors, Gold Plating, 20-18 AWG, Right Reel Payoff	<u>330012004</u>
MX150 Female Terminal for Mat-Sealed Connectors, Gold Plating, 22 AWG, Right Reel Payoff	<u>330012005</u>
MX150 Female Terminal for Unsealed Connectors, Gold Plating, 16-14 AWG, Right Reel Payoff. Not suitable for MX150 Sealed Connectors.	<u>330012021</u>
MX150 Female Terminal for Unsealed Connectors, Gold Plating, 20-18 AWG, Right Reel Payoff. Not suitable for MX150 Sealed Connectors.	<u>330012022</u>
MX150 Female Terminal for Unsealed Connectors, Gold Plating, 22 AWG, Right Reel Payoff . Not suitable for MX150 Sealed Connectors.	<u>330012023</u>
MX150 Female Terminal for Mat-Sealed Connectors, Gold Plating, 16-14 AWG, Left Reel Payoff	<u>330013003</u>

MX150 Female Terminal for Mat-Sealed Connectors, Gold Plating, 20-18 AWG, Left Reel Payoff	<u>330013004</u>
MX150 Female Terminal for Mat-Sealed Connectors, Gold Plating, 22 AWG, Left Reel Payoff	<u>330013005</u>
MX150 Female Terminal for Unsealed Connectors, Gold Plating, 16-14 AWG, Left Reel Payoff. Not suitable for MX150 Sealed Connectors.	<u>330013021</u>
MX150 Female Terminal for Unsealed Connectors, Gold Plating, 20-18 AWG, Left Reel Payoff. Not suitable for MX150 Sealed Connectors.	<u>330013022</u>
MX150 Female Terminal for Unsealed Connectors, Gold Plating, 22 AWG, Left Reel Payoff. Not suitable for MX150 Sealed Connectors.	<u>330013023</u>
MX150 Female Terminal for Mat-Sealed Connectors, Silver Plating, 16-14 AWG, Right Reel Payoff	<u>330014001</u>
MX150 Female Terminal for Mat-Sealed Connectors, Silver Plating, 20-18 AWG, Right Reel Payoff	<u>330014002</u>
MX150 Female Terminal for Mat-Sealed Connectors, Silver Plating, 22 AWG, Right Reel Payoff	<u>330014003</u>
MX150 Female Terminal for Unsealed Connectors, Silver Plating, 16-14 AWG, Right Reel Payoff. Not suitable for MX150 Sealed Connectors.	<u>330014021</u>
MX150 Female Terminal for Unsealed Connectors, Silver Plating, 20-18 AWG, Right Reel Payoff. Not suitable for MX150 Sealed Connectors.	<u>330014022</u>
MX150 Female Terminal for Unsealed Connectors, Silver Plating, 22 AWG, Right Reel Payoff.	<u>330014023</u>

Not suitable for MX150 Sealed Connectors.	
MX150 Female Terminal for Mat-Sealed Connectors, Silver Plating, 16-14 AWG, Left Reel Payoff	<u>330015001</u>
MX150 Female Terminal for Mat-Sealed Connectors, Silver Plating, 20-18 AWG, Left Reel Payoff	<u>330015002</u>
MX150 Female Terminal for Mat-Sealed Connectors, Silver Plating, 22 AWG, Left Reel Payoff	<u>330015003</u>
MX150 Female Terminal for Unsealed Connectors, Silver Plating, 16-14 AWG, Left Reel Payoff. Not suitable for MX150 Sealed Connectors.	<u>330015021</u>
MX150 Female Terminal for Unsealed Connectors, Silver Plating, 20-18 AWG, Left Reel Payoff. Not suitable for MX150 Sealed Connectors.	<u>330015022</u>
MX150 Female Terminal for Unsealed Connectors, Silver Plating, 22 AWG, Left Reel Payoff. Not suitable for MX150 Sealed Connectors.	<u>330015023</u>
MX150 Female Terminal for Mat-Sealed Connectors, Tin Plating, 16-14 AWG, Right Reel Payoff	<u>330122001</u>
MX150 Female Terminal for Mat-Sealed Connectors, Tin Plating, 20-18 AWG, Right Reel Payoff	<u>330122002</u>
MX150 Female Terminal for Mat-Sealed Connectors, Tin Plating, 22 AWG, Right Reel Payoff	<u>330122003</u>
MX150 Female Terminal for Unsealed Connectors, Tin Plating, 16-14 AWG, Right Reel Payoff. Not suitable for MX150 Sealed Connectors.	<u>330122021</u>
MX150 Female Terminal for Unsealed Connectors, Tin Plating,	<u>330122022</u>

20-18 AWG, Right Reel Payoff. Not suitable for MX150 Sealed Connectors.	
MX150 Female Terminal for Unsealed Connectors, Tin Plating, 22 AWG, Right Reel Payoff. Not suitable for MX150 Sealed Connectors.	<u>330122023</u>
MX150 Female Terminal for Mat-Sealed Connectors, Tin Plating, 16-14 AWG, Left Reel Payoff	<u>330123001</u>
MX150 Female Terminal for Mat-Sealed Connectors, Tin Plating, 20-18 AWG, Left Reel Payoff	<u>330123002</u>
MX150 Female Terminal for Mat-Sealed Connectors, Tin Plating, 22 AWG, Left Reel Payoff	<u>330123003</u>
MX150 Female Terminal for Unsealed Connectors, Tin Plating, 16-14 AWG, Left Reel Payoff. Not Suitable for MX150 Sealed Connectors.	<u>330123021</u>
MX150 Female Terminal for Unsealed Connectors, Tin Plating, 20-18 AWG, Left Reel Payoff. Not Suitable for MX150 Sealed Connectors.	<u>330123022</u>
MX150 Female Terminal for Unsealed Connectors, Tin Plating, 22 AWG, Left Reel Payoff. Not suitable for MX150 Sealed Connectors.	<u>330123023</u>

This document was generated on Sep 13, 2025