

AB3/SS - Support bracket



0800086
<https://www.phoenixcontact.com/us/products/0800086>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Support bracket, material: PA, mounting type: Direct mounting, color: gray



Commercial data

Item number	0800086
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE07
Product key	BE7113
GTIN	4046356613774
Weight per piece (including packing)	9.15 g
Weight per piece (excluding packing)	8.21 g
Customs tariff number	85472000
Country of origin	CN

AB3/SS - Support bracket



0800086

<https://www.phoenixcontact.com/us/products/0800086>

Technical data


Product properties

Product type	Support bracket
Number of positions	3.00

Electrical properties

Nominal current I _N	0 A
--------------------------------	-----

Dimensions

Dimensional drawing	
Diameter	4.5 mm

Material specifications

Color	gray (RAL 7042)
Material	PA
Flammability rating according to UL 94	V0
Static insulating material application in cold	-60 °C
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	130 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

Mounting

Mounting type	Direct mounting
---------------	-----------------

AB3/SS - Support bracket


0800086

<https://www.phoenixcontact.com/us/products/0800086>



Drawings

Dimensional drawing



AB3/SS - Support bracket



0800086
<https://www.phoenixcontact.com/us/products/0800086>

Classifications

ECLASS

ECLASS-13.0	27400607
ECLASS-15.0	27400607

ETIM

ETIM 9.0	EC001166
----------	----------

UNSPSC

UNSPSC 21.0	39121700
-------------	----------

AB3/SS - Support bracket



0800086
<https://www.phoenixcontact.com/us/products/0800086>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com