Part Number : 347960201
Product Description : MX150 Cable Unsealed Female Connector, Single Row, 2 Circuits, Keying Option A, Black
Series Number : 34796
Status : Obsolete
Product Category : Connector Housings



Obsolete

Documents and Resources

Drawings

347960201_sd.pdf

Specifications

AS-34796-001-001.pdf

PS-34796-001-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant
China RoHS	per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

Downloaded from Arrow.com.

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Connector Housings
Series	34796
Description	MX150 Cable Unsealed Female Connector, Single Row, 2 Circuits, Keying Option A, Black
Application	Wire-to-Wire, Automotive
Component Type	Receptacle
Product Name	MX150 Unsealed
UPC	884982969445

Physical

Circuits (maximum)	2
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Polybutylene Terephthalate (PBT)
Net Weight	2.010/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.50mm
Pitch - Termination Interface	3.50mm
Polarization	A
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C

Obsolete

Downloaded from Arrow.com.

Solder Process Data

Lead-Free Process Capability	N/A

Mates With / Use With

Mates with Part(s)

Description	Part Number
MX150 Cable Unsealed Male Connectors	34797

Use with Part(s)

Description	Part Number
MX150 Female Terminal for Unsealed Connectors, Tin Plating, 16-14 AWG, Right Reel Payoff. Not suitable for MX150 Sealed Connectors.	330122021
MX150 Female Terminal for Unsealed Connectors, Tin Plating, 20-18 AWG, Right Reel Payoff. Not suitable for MX150 Sealed Connectors.	330122022
MX150 Female Terminal for Unsealed Connectors, Tin Plating, 22 AWG, Right Reel Payoff. Not suitable for MX150 Sealed Connectors.	330122023
MX150 Female Terminal for Unsealed Connectors, Tin Plating, 16-14 AWG, Left Reel Payoff. Not Suitable for MX150 Sealed Connectors.	330123021
MX150 Female Terminal for Unsealed Connectors, Tin Plating, 22 AWG, Left Reel Payoff. Not suitable for MX150 Sealed Connectors.	330123023

Obsolete

Downloaded from Arrow.com.