Part Number : 988241010
Product Description : NSCC Pin Connector, Unsealed, 2.8mm, 5.00mm Pitch, 2 Circuits, White
Series Number : 98824
Status : Obsolete
Product Category : Connector Housings
Engineering Part Number : 08219EV2F9



Documents and Resources

Drawings

988241010_sd.pdf

PK-98824-001-001.pdf

Specifications

AS-98821-001-001.pdf

988210001-AS-CH-001.pdf

988210001-PS-CH-001.pdf

PS-98821-001-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant
China RoHS	Not Relevant
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D

Obsolete

Downloaded from Arrow.com.

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Connector Housings
Series	98824
Description	NSCC Pin Connector, Unsealed, 2.8mm, 5.00mm Pitch, 2 Circuits, White
Application	Wire-to-Wire
Component Type	Plug
Product Name	NSCC
UPC	822348760411

Physical

Circuits Detail	2x2.80mm pins
Circuits (maximum)	2
Color - Resin	White
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	4.660/g
Number of Rows	1
Packaging Type	Carton
Panel Mount	No
Pitch - Mating Interface	5.00mm
Polarized to Mating Part	Yes

Obsolete

Downloaded from Arrow.com.

Ports	1
Stackable	No
Temperature Range - Operating	-40° to +85°C

Solder Process Data

Lead-Free Process Capability	N/A

Mates With / Use With

Mates with Part(s)

Description	Part Number
NSCC Unsealed Pin Connectors	98824

Application Tooling

Global

Description	Part Number
Extractor Tool for Unsealed Receptacle Connectors	638133800

This document was generated on Aug 29, 2026

Obsolete

Downloaded from Arrow.com.