




HTWD Halogen Free Wiring Duct HTWD-HF-25X50

HelaDuct HTWD-HF (DIN sizes), Article number: 183-12550



Images (4)

Downloads



Features

- Excellent fire-safety characteristics
- Narrow slots suitable for small-diameter wires
- Smooth, burr-free edges protect installers from injury and wires from damage
- Fingers can be removed with no sharp edges at pre-notched snap-off points
- Further pre-notched snap-off point at base of sidewall allow cutting out and removing sections of sidewall with no sharp edges
- Duct covers hold securely even in a vertical position and under vibration
- Cover is flush with side of duct, allowing for tight, contiguous placement of duct
- Base perforation according to DIN EN 50085

Certifications & Approvals



Application

HellermannTyton HTWD-HF halogen-free ducts are used wherever there are high demands on personal or material safety, such as public transport, tunnels, lifts and data processing centres.
Note: Halogen-free PC+ABS is not resistant to all oils and greases.

HelaDuct HTWD-HF (DIN sizes) is suitable for following markets and industries

Electrical Installation

Rail Transportation Sector

Panell Building

More products in this product group

[HTWD Halogen Free Wiring Duct >](#)

Base Data


Application Tool	4FTOOL
Colour	Grey RAL 7035 (RAL7035)
Current leak stable Yes/No	Yes
Description Short (BMEcat) (max. 150 characters)	Wiring duct 25x50 mm, 2000 mm, PC/ABS, grey
Fixation Method	Screw Mounting
GLOBAL PART DESCRIPTION	HTWD-HF-25X50-PC/ABS-GY
Pack Cont.	44
Package Quantity per	box
Product Family	HelaDuct HTWD-HF (DIN sizes)

Type of side wall	Slotted
-------------------	---------

Product Dimensions

Height (H)	50 mm
Length (L)	2 m
Suitable for cross section	825 mm ²
Width (W)	25 mm
Width (W2)	5.0 mm
Width (W3)	7.5 mm

Material and Specifications


ELV compliant (Article 4 - 2)	YES
EN 45545-2 Results	R22 HL2, R23 HL2
Flammability	UL 94 V0
Halogenfree	Yes
Hazardous good	No
Material	Acrylonitrile Butadiene Styrene alloyed with Polycarbonate (PC/ABS)
Operating Temperature - °C	-25 °C to +90 °C, intermittent +100 °C
Specifications	   
Specifications	DIN EN 45545-2 (02/2016), ISO11925, NF F 16-101

Logistics and Packaging


More Information

ETIM 5.0	EC000012
ETIM 6.0	EC000012
UNSPSC Key	39131712

Further information to HTWD-HF-25X50

 Technical drawing 10-0777-001-CSG  Download >	 CAD-Download Download >
--	--

Competences



Wiring ducts and accessories from HelaDuct: optimum protection for cables and fitters.

Discover the advantages of HelaDuct wiring ducts system solutions with its special space-saving shapes: these unique wiring ducts are designed for height and give you more lateral space. They come with blunted edges that protect the cable insulation and make them safer to work with during installation and maintenance. HelaDuct products are used in switch cabinets and switching stations and are very well suited to cables with small cross sections.

[Wiring ducts >](#)

Accessories



4FTOOL
182-96000

Similar products



HTWD-HF-25X25
183-12525
HTWD Halogen Free
Wiring Duct



HTWD-HF-37.5X37.5
183-13737
HTWD Halogen Free
Wiring Duct



HTWD-HF-37.5X50
183-13750
HTWD Halogen Free
Wiring Duct



HTWD-HF-37.5X75
183-13775
HTWD Halogen Free
Wiring Duct



HTWD-HF-50X50
183-15050
HTWD Halogen Free
Wiring Duct



HTWD-HF-50X75
183-15075
HTWD Halogen Free
Wiring Duct

[Show all ▾](#)

Stay in touch with us!



Global Company

About us
Worldwide
Philosophy
Environment & Quality
Corporate Social
Responsibility
Product Development
E-Business
ACADEMY
Careers
MADE FOR REAL

Products

Product overview
Cable Ties and Fixings
Insulation
Cable Protection Systems
Electrical Installation
Identification Systems
Application Tooling
Connectivity

Competences

Cable Ties
Heat Shrink Tubing
Industrial Identification
and Self-Adhesive Labels
Cable Protection
Conduits
Electrical Installation
Electrical tape
Wire connectors
Cable rods
Downlight covers
Cable jointing
Gel-filled cable joints
Cable Tie Guns
Connectivity Products
RFID tracking
Cable tie mounts
Thermal Transfer Printer
P-Clamp
Wiring ducts

Markets & Industries

Automotive Industry
Solar plants
Wind turbines
Shipbuilding
Panel building
Rail industry
Food Industry
Chemical Industry
Aerospace Industry
Defence Industry

Media Centre

Videos
Product Catalogue
2018/2019
Automotive Catalogue
2016/2017
Connectivity Catalogues
2016/2017
Brochures
Software & Drivers
Helatag & Helafix
Templates
Manuals & Operating
Instructions

Cable clips for edges
Cable management high
temperature
applications

Events

Update: 07/10/2018

You can easily accept or reject the cookies on this site by choosing one of the following links:

[I accept cookies](#)

[I refuse cookies](#)

[Privacy](#)

[Contact](#) [Terms of Service](#) [Imprint](#) [Privacy Policy](#)

[statement](#)