




Part Number : [2002188600](#)
Product Description : Hand Crimp Tool for 10.00mm Pitch Mini-Fit Sr. Crimp Terminals, 10-12 AWG
Series Number : 207129
Status : Active
Product Category : Crimp Presses and Crimp Hand Tools



Documents & Resources

Tooling Specifications
[Application Tooling Specification 2002188600-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Not Reviewed per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Crimp Presses and Crimp Hand Tools
Series	207129
Description	Hand Crimp Tool for 10.00mm Pitch Mini-Fit Sr. Crimp Terminals, 10-12 AWG
Comments	See Tooling Specification (PDF) Above
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Product Family	Application Tooling
Product Name	Mini-Fit Sr.
Tool Type	Hand Crimp Tool
UPC	193264551811
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical

Net Weight	680.000/g
------------	-----------

Applicable Parts

Global

Description	Part Number
Mini-Fit Sr. Crimp Terminal, Female, 10-12 AWG, Gold (Au)	<u>0428150012</u>
Mini-Fit Sr. Crimp Terminal, Female, 10-12 AWG, Silver (Ag)	<u>0428150114</u>
Mini-Fit Sr. Crimp Terminal, Male, 10-12 AWG, Gold (Au)	<u>0428170012</u>
Mini-Fit Sr. Crimp Terminal, Male, 10-12 AWG, Gold (Au)	<u>0428170112</u>
Mini-Fit Sr. Crimp Terminal, Male, 10-12 AWG, Silver (Ag)	<u>0428171014</u>
Mini-Fit Sr. Crimp Terminal, Male, 10-12 AWG, Silver (Ag)	<u>0428171114</u>

This document was generated on Sep 12, 2023