

ETS-E - Label with ground icon



0806767

<https://www.phoenixcontact.com/us/products/0806767>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Label, self-adhesive, 16 mm diameter, available as: 100 sheets with 10 labels each, black grounding symbol on white background



Commercial data

Item number	0806767
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	BG20
Product key	BG2424
GTIN	4017918138882
Weight per piece (including packing)	0.564 g
Weight per piece (excluding packing)	0.05 g
Customs tariff number	39191080
Country of origin	DE

ETS-E - Label with ground icon



0806767

<https://www.phoenixcontact.com/us/products/0806767>

Technical data

Product properties

Product type	Labeled device marker
--------------	-----------------------

Marking

Number of individual labels	10
-----------------------------	----

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1.0 S
Cycles	2

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed

Ambient conditions

Shelf life	2 years
------------	---------

Mounting

Mounting type	adhesive
---------------	----------

Material specifications

Foil strength	92 µm
Adhesive	Acrylic
Color	white (RAL 9010)

ETS-E - Label with ground icon



0806767

<https://www.phoenixcontact.com/us/products/0806767>

Material	Polyethylene
----------	--------------

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1.0 S
Cycles	2

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed

Ambient conditions

Shelf life	2 years
------------	---------

Dimensions

Width	16 mm
Length	0 mm

Standards and regulations

Wipe resistance	DIN 30646 DIN VDE 0611-1
-----------------	-----------------------------

ETS-E - Label with ground icon



0806767

<https://www.phoenixcontact.com/us/products/0806767>

Classifications

ECLASS

ECLASS-13.0	40200202
ECLASS-15.0	40200202

ETIM

ETIM 9.0	EC001777
----------	----------

UNSPSC

UNSPSC 21.0	55121700
-------------	----------

ETS-E - Label with ground icon



0806767
<https://www.phoenixcontact.com/us/products/0806767>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com