

# GRM32EC70J107ME15#

“#” indicates a package specification code.




## < List of part numbers with package codes >

GRM32EC70J107ME15L      GRM32EC70J107ME15K

## Applications

|                         |                                                                                                                                                                                                                                                                                                                                                                                                                                             |
|-------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Unsuitable Applications | Please be sure to read and comply with these "Precautions for use."                                                                                                                                                                                                                                                                                                                                                                         |
| Specific Applications   | Consumer equipment, Industrial Equipment, Mobile Electronics, Medical equipment [GHF A/B/C] except for implant equipment, Automotive infotainment/comfort equipment<br>Please refer to Our Website and specifications, etc. for information about the performance, functions, quality, management, and safety required for the above applications, and use Products after confirming the performance and reliability of the actual Product. |

## Appearance & Shape



## Notices

Derating1

## References

| Packaging | Specifications    | Standard Packing Quantity |
|-----------|-------------------|---------------------------|
| L         | 180 Embossed Tape | 1000                      |
| K         | 330 Embossed Tape | 4000                      |

| Mass (typ.) |         |
|-------------|---------|
| 1 piece     | 110.0mg |

### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, its specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# GRM32EC70J107ME15#

“#” indicates a package specification code.



## Specifications

|                                                  |                |
|--------------------------------------------------|----------------|
| Length                                           | 3.2±0.3mm      |
| Width                                            | 2.5±0.2mm      |
| Thickness                                        | 2.5±0.2mm      |
| Capacitance                                      | 100μF ±20%     |
| Distance between external terminals g            | 1.0mm min.     |
| External terminal size e                         | 0.3mm min.     |
| Operating Temperature Range                      | -55°C to 125°C |
| Rated Voltage                                    | 6.3Vdc         |
| Size code in inch(mm)                            | 1210 (3225M)   |
| Capacitance change rate                          | ±22.0%         |
| Temperature characteristics (complied standard)  | X7S(EIA)       |
| Temperature range of temperature characteristics | -55°C to 125°C |

### Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.


# GRM32EC70J107ME15#

"#" indicates a package specification code.




## Characteristic Data


The charts below may show another part number which shares its characteristics.




GRM32EC70J107ME15 |Z| DCOV,25degC



GRM32EC70J107ME15 R DCOV,25degC



GRM32EC70J107ME15 C-DC bias capchange, 25.0C



GRM32EC70J107ME15 C-AC Voltage capchange, Dc

### Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# GRM32EC70J107ME15#

“#” indicates a package specification code.

