

Home → Tool Types → L-Keys → TorxPlus® L-Keys Long Arm

TorxPlus® L-Keys Long Arm



Zoom

Titles and descriptions supersede the photo. We typically use the same image for different sizes of tools.

Be the first to review this product

Filter:

SKU	Product	Price	Qty
36606	TorxPlus® L-Key Long Arm IP6 x 64mm		0
36607	TorxPlus® L-Key Long Arm IP7 x 68mm		0
36608	TorxPlus® L-Key Long Arm IP8 x 74mm		0
36609	TorxPlus® L-Key Long Arm IP9 x 78mm		0
36610	TorxPlus® L-Key Long Arm IP10 x 83mm		0
36615	TorxPlus® L-Key Long Arm IP15 x 88mm		0
36620	TorxPlus® L-Key Long Arm IP20 x 94mm		0
36625	TorxPlus® L-Key Long Arm IP25 x 98mm		0
36627	TorxPlus® L-Key Long Arm IP27 x 107mm		0
36630	TorxPlus® L-Key Long Arm IP30 x 114mm		0

SKU	Product	Price	Qty
36640	TorxPlus® L-Key Long Arm IP40 x 118mm		0 

Add to Cart

-  Add to Wishlist
-  Share on Facebook
-  Tweet This
-  Pin it

We accept 

Details

Corrosion protected Black Finish
Long Arms are 15 to 20% longer
Wiha special chrome-vanadium-molybdenum tool steel
Precision Machined TorxPlus Tips for exact fit & long life
Up to 100% Better Drive performance over standard TORX
TorxPlus Virtually eliminates screw head cam-out
TorxPlus tools may not fit in standard TORX head screws
Through hardened for best wear resistance

Additional Info

Head Type	  torx plus
Country of Manufacture	Germany
Handle Style	L-Key
L-Key Features	Short Arm

WRITE YOUR OWN REVIEW

Only registered users can write reviews. Please, [log in](#) or [register](#)

Warranty Info

Wiha Products Carry a **100% Satisfaction Guarantee**. All Wiha tools are guaranteed to be free of defects in workmanship and materials and will be replaced if found to be deficient providing tools have not been altered or misused. Wiha Insert Bits, Power Bits, Ceramic Tools and Tweezers are not warranted for use. Wiha Brand Torque control Tools are warranted for twelve months from date of purchase up to 5,000 torque Cycles.

[View Full Warranty](#)

You may also be interested in the following product(s)



TorxPlus® Long Arm L-Key 9 Piece
Set IP8-IP40



We produce Wiha products around the world under strict ISO quality standards. State of the art technology and special tool steels

assure products consistent with our reputation for outstanding performance in demanding service, repair and production applications.

[Discounts and promotions](#)

[Military Discount](#)

[IBEW-NECA Discount](#)

[Filter and sort all Wiha hand tools](#)

[Complete list of tools](#)

1985 bringing Wiha quality to professional tool users in North America. Our USA warehouse and distribution center services all 50 states & Our New Facilities In Canada Supply millions of tools from stock to professional quality conscious tool users throughout North America.

[About Us](#)

[Privacy Policy](#)

[Terms and Conditions](#)

[Having technical issues with the website?](#)

We accept



A Subsidiary of [Wiha Werkzeuge Gmbh](#)
[Schonach Germany](#)

**Monday - Friday Office Hours 7am - 5pm
CST USA**

1348 Dundas Cir,
Monticello, MN 55362
Customer Service Email:
cservice@wihatools.com
Tel: **763-295-6591**
Fax: 763-295-6598

[Shipping](#)

[Returns](#)

[Warranty Info](#)

[About Us](#)

[Privacy Policy](#)

[Terms and Conditions](#)

**Over 5000 Professional Quality Wiha Tools
In Stock**



Newsletter

[Subscribe](#)

© 2017 Wiha Tools USA. All Rights Reserved.

SHIPS FREE

