

**Part Number :** [192020056](#)

**Product Description :** NylaKrimp Butt Splice for 4 AWG Wire, Carton

**Series Number :** 19202

**Status :** Active

**Product Category :** Splices

**Engineering Part Number :** F-764



---

## Documents and Resources

### Drawings

[192020056\\_sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)


### Specifications

[PS-19902-013-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2021)4569-DC (8 July 2021)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

## Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	Splices
Series	19202
Description	NylaKrimp Butt Splice for 4 AWG Wire, Carton
Product Name	NylaKrimp
Style	Standard
Type	Butt Splice
UPC	800753048348

### Agency

CSA	LR18689
UL	E32244

### Electrical

Voltage - Maximum	300V
-------------------	------

### Physical

Barrel Type	Closed - Brazed
Color - Resin	Yellow
Flammability	94V-2
Insulation	Nylon (PA)
Material - Metal	Copper

Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	16.343/g
Packaging Type	Carton
Temperature Range - Operating	-55° to +105°C
Wire Insulation Diameter	10.92mm max.
Wire Size (AWG)	4

---

## Application Tooling

### Global

Description	Part Number
Putt Pump Hydraulic Head Crimper, Die Set Required, For Insulated and Non-Insulated Terminals and Splices	<u>192860117</u>
Die Set (Large) for the HHLS Hydraulic Crimper	<u>192890007</u>
PremiumGrade Hand Crimp Tool for 8-2 AWG Terminals	<u>640013900</u>
Hand Crimp Tool for 4 AWG Insulated Ring Terminals	<u>640017870</u>

---

This document was generated on Dec 29, 2025