

- Product Catalog

○ Product Search

○ Product Inquiry

○ Applications

○ Automotive

○ Industrial

○ Information & Communications

○ Consumer

○ Design Support

○ Publications

○ Environmental Protection
- COMPONENTS Magazine
- Company Profile
- Press Center
- Corporate Responsibility
- Jobs and Career
- Events
- Contact
- TDK-EPC
- TDK Components

Medical appliances

- ✚ [Power supply & conversion](#)

✚ [Power Quality Solutions](#)

✚ [Ballast systems](#)

✚ [Automation](#)
- ✚ [Medical appliances](#)

✚ [Wind energy](#)

✚ [Photovoltaic systems](#)

✚ [Heat exchanger systems](#)

Please click the application for details on the product range.
The complete application guide and product portfolio for medical appliances are also available in PDF format.

-  [Application Guide \(1.6 MB\)](#)
-  [Portfolio Overview \(40 KB\)](#)



- ✚ [Anesthesia equipment](#)

✚ [Cleaning equipment](#)

✚ [Clinical thermometers](#)

✚ [Computed tomography](#)

✚ [Defibrillation devices](#)

✚ [Glucose meters](#)

✚ [Magnetic resonance imaging](#)

✚ Patient care monitoring

✚ [Respiration technology](#)

✚ [Ultrasound imaging systems](#)
- ✚ [X-ray equipment](#)

Patient care monitoring

Please click the product group for technical details

- ▶ [EMC filters](#)

✚ [Medical appliances-specific features](#)
- ▶ [Film Capacitors](#)

✚ [Medical appliances-specific features](#)
- ▶ [Inductors](#)

✚ [Medical appliances-specific features](#)
- ▶ [NTC thermistors](#)

✚ [Medical appliances-specific features](#)
- ▼ [SAW components](#)

✚ [Medical appliances-specific features](#)

	Series/Features	Center frequency (MHz)	Usable Passband (MHz)	Ordering code	PDF
	Ceramic 50 Ω terminating impedance - Operating temperature $-40 \dots +125 \text{ }^{\circ}\text{C}$ - US and Europe ISM bands - Small SMD package size: $3.0 \times 3.0 \times 1.1 \text{ mm}$ (typ.) ✚ Product Search	315	1	B39321B3722U410	
		433.92	1.6	B39431B3721U410	
	CSSP3 50 Ω terminating impedance - Operating temperature $-40 \dots +85 \text{ }^{\circ}\text{C}$ - US and Europe ISM bands - Small SMD package size: $1.4 \times 1.1 \times 0.4 \text{ mm}$ (typ.) ✚ Product Search	869	2	B39871B4316P810	
		915	26	B39921B4301F210	
	CSSP3 - Bluetooth 4.0 - BT EDR (2 and 3 Mbps) - WLAN 802.11 a/b/g/n - Small SMD package size: $1.4 \times 1.1 \times 0.4 \text{ mm}$ (typ.) $F_c = 2441.75 \text{ MHz}$, usable BW 83.5 MHz $F_c = 2450 \text{ MHz}$, usable BW 100 MHz ✚ Product Search	-		B39242B9413K610	
				B39252B9455M410	
	D7002 - WLAN 802.11 a/b/g/n - Bluetooth 4.0 - BT EDR (2 and 3 Mbps) - GPS - FM (Tx/Rx) - Fully integrated module supporting WiFi, BT, GPS and FM - Embedded TI connectivity IC (WL1283) - Fully shielded, tested turnkey module solution - Small SMD package size: $11.9 \times 9.5 \times 1.2 \text{ mm}$ (typ.)			B30961D7002Y910	
▶ Varistors				✚ Medical appliances-specific features	
✚ Back					