

# KGG-MSTB 2,5/ 8 - Cable housing

1803921

<https://www.phoenixcontact.com/us/products/1803921>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cable housing, product range: KGG-MSTB 2,5, width: 19 mm



## Commercial data

Item number	1803921
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AA08
Product key	AAHZDC
GTIN	4017918046071
Weight per piece (including packing)	11.36 g
Weight per piece (excluding packing)	10.3 g
Customs tariff number	39269097
Country of origin	PL

# KGG-MSTB 2,5/ 8 - Cable housing

1803921

<https://www.phoenixcontact.com/us/products/1803921>



## Technical data

### Product properties

Product type	Cable housing
Product family	KGG-MSTB 2,5
Number of positions	8
Pitch	0 mm

### Mounting

#### Cable clamp

Tightening torque	0.2 Nm
-------------------	--------

### Material specifications

Flammability rating according to UL 94	HB
Insulating material	ABS
Insulating material group	I
CTI according to IEC 60112	600
Flammability rating according to UL 94	HB

### Dimensions

Width	19 mm
Height	37 mm
Pitch	-

### Notes

General	COMBICON connection plugs can be ordered separately.
---------	------------------------------------------------------

# KGG-MSTB 2,5/ 8 - Cable housing

1803921

<https://www.phoenixcontact.com/us/products/1803921>



## Classifications

### ECLASS

ECLASS-13.0	27460402
ECLASS-15.0	27460402

### ETIM

ETIM 9.0	EC002943
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# KGG-MSTB 2,5/ 8 - Cable housing

1803921

<https://www.phoenixcontact.com/us/products/1803921>



## Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.0 Climate Change	
CO2e kg	0.071 kg CO2e

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)