



**Part Number :** [08520071](#)  
**Product Description :** KK 396 Crimp Terminal  
2478, 24-18 AWG, Reel, Phosphor Bronze, Tin  
(Sn)  
**Series Number :** 2478  
**Status :** Active  
**Product Category :** Crimp Terminals  
**Engineering Number :** 2478-3-(P909)  
**Packaging Alternative :** [08520072 \(Bag\)](#)




Documents & Resources

**Drawings**  
[008520071\\_sd.pdf](#)

**Specifications**  
[PS-08-50-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## EU RoHS Certificate of Compliance

---

### Part Details

#### General

Status	Active
Category	Crimp Terminals
Series	2478
Description	KK 396 Crimp Terminal 2478, 24-18 AWG, Reel, Phosphor Bronze, Tin (Sn)
Application	Power, Wire-to-Board
Product Name	KK 396, KK 508
UPC	800753758131

#### Physical

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.198/g
Packaging Type	Reel
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	2.79mm max.
Wire Size (AWG)	18, 20, 22, 24
Wire Size mm <sup>2</sup>	N/A

#### Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

---

#### Use with Part(s)

Description	Part Number
KK 3.96mm Single Row Crimp Housings	<u>2139</u>
KK 3.96mm Single Row Crimp Housings	<u>3069</u>
KK 3.96mm Crimp Housings	<u>41695</u>

---

## Application Tooling

### Global

Description	Part Number
Extraction Tool for Flat Blade, 3.96mm KK, 2.00mm, 3.96mm EdgeMate, and Ultra-Fit Terminals	<u>11030016</u>
Terminator Die	<u>11402096</u>
Hand Crimp Tool for 3.96mm Pitch KK Crimp Terminals, 24-18 AWG	<u>638279500</u>
Mini-Mac Applicator for KK and Trifurcon, 3.96mm Terminals, 24-18 AWG, check ATS for Wire Insulation Diameter Compatibility	<u>638885000</u>

---

This document was generated on Mar 22, 2025