

Connectors > Rectangular Connectors > Rectangular Contact Inserts

4-1197382-6 ACTIVE

Rectangular Contact Inserts, Insert for Contacts, Pin, Wire-to-Wire, 20 Position, Sealable, 22 – 20 AWG Wire Size, .34 – .5 mm² Wire Size, 1.5 A



RAYCHEM

TE Internal #: 953371-000
TE Internal Description: MTCP-122-20P

Rectangular Connector Insert Type : **Insert for Contacts**
Contact Type : **Pin**
Connector System : **Wire-to-Wire**
Number of Positions : **20**
Centerline (Pitch) : **1.27 mm [.05 in]**

Add to List | Similar Products | Digital Datasheet

Compatible Parts & Tooling

Documents	Features	Product Compliance
Please review product documents or contact us for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.		
Product Type Features	Rectangular Connector Insert Type : Insert for Contacts Connector System : Wire-to-Wire Sealable : Yes Connector & Contact Terminates To : Wire & Cable	
Configuration Features	Number of Positions : 20	
Body Features	Primary Product Color : Black Primary Product Material : High Grade Polyarylene Thermoplastic Seal Type : Grommet Seal, Interfacial Seal	
Contact Features	Contact Type : Pin Contact Current Rating (Max) (A): 1.5	
Mechanical Attachment	Polarization Code : A/B Connector Mounting Type : Panel Mount	
Housing Features	Centerline (Pitch) : 1.27 mm [.05 in]	
Dimensions	Wire Size (AWG): 22 – 20 Wire Size (mm²): .34 – .5	
Usage Conditions	Operating Temperature Range : -65 – 125 °C [-85 – 257 °F]	
Operation/Application	Compatible With Connector Shell Size : 25.4 [1.0]	

Compatible Parts

ACCESSORY

CTA-0166

Pin Contact, 26 – 20 AWG Wire Size, .14 – .5 mm² Wire...

In-Stock

[VIEW PRODUCT](#)

Filter By Specification

Products with Similar Specs

[View All Similar Products](#)

THIS PRODUCT

RECTANGULAR CONTACT INSERTS

4-1197382-6

Rectangular Contact Inserts, Insert for Contacts, Pin, Wire-to-Wire, 20...

In-Stock

Rectangular Connector Insert Type : **Insert for Contacts**
Contact Type : **Pin**
Connector System : **Wire-to-Wire**
Number of Positions : **20**
Centerline (Pitch) : **1.27 mm**

TOP RESULTS

RECTANGULAR CONTACT INSERTS

MTCP-122-20PQ

Rectangular Contact Inserts, Insert for Contacts, Pin, Wire-to-Wire, 20...

In-Stock

Rectangular Connector Insert Type : **Insert for Contacts**
Contact Type : **Pin**
Connector System : **Wire-to-Wire**
Number of Positions : **20**
Centerline (Pitch) : **1.27 mm**

RECTANGULAR CONTACT INSERTS

MTCP-122-20PQ2

Rectangular Contact Inserts, Insert for Contacts, Pin, Wire-to-Wire, 20...

In-Stock

Rectangular Connector Insert Type : **Insert for Contacts**
Contact Type : **Pin**
Connector System : **Wire-to-Wire**
Number of Positions : **20**
Centerline (Pitch) : **1.27 mm**

RECTANGULAR CONTACT INSERTS

7-1194775-9

Rectangular Contact Inserts, Insert for Contacts, Pin, Wire-to-Wire, 20...

In-Stock

Rectangular Connector Insert Type : **Insert for Contacts**
Contact Type : **Pin**
Connector System : **Wire-to-Wire**
Number of Positions : **20**
Centerline (Pitch) : **1.27 mm**

Customers Also Bought

TE Part #: **749808-7**

Crimp D-Sub Connectors, Plug, Cable-to-Cable, 25...

\$18.667 per unit

Inventory: In-Stock

[Add To Cart](#)

TE Part #: **207252-2**

Box Mount D-Sub Connectors, Plug...

\$99.540 per unit

Inventory: In-Stock

[Add To Cart](#)

TE Part #: **204370-8**

Pin Contact, Gold, Size 22

Contact Size, 28 – 22 AWG...

\$1.290 per unit

Inventory: In-Stock

[Add To Cart](#)

TE Part #: **205089-4**

Pin Contact, Gold, Size 20

Contact Size, 24 – 20 AWG...

\$2.010 per unit

Inventory: In-Stock

[Add To Cart](#)

TE Part #: **206501-4**

Box Mount D-Sub Connectors, Receptacle...

\$148.430 per unit

Inventory: In-Stock

[Add To Cart](#)

TE Part #: **206501-4**

Box Mount D-Sub Connectors, Receptacle...

\$148.430 per unit

Inventory: In-Stock

[Add To Cart](#)

TE Part #: **206501-4**

Box Mount D-Sub Connectors, Receptacle...

\$148.430 per unit

Inventory: In-Stock

[Add To Cart](#)

Contact Our Team – 24/7 Support

+1 800 522 6752

Live Chat

[See Support Details](#)

Connect With Us

Access Partner Information

[Distributors](#)

[Suppliers](#)

[Supplier Diversity](#)

Get Answers Now

[Authorized Distributors & Resellers](#)

[Product FAQs](#)

[Samples FAQs](#)

[TE Store FAQs](#)

[Terms and Conditions of Sale](#)

[Samples Terms and Conditions](#)

Select Your Preferences

Language

[English \(EN\)](#)

Ship to

United States (\$USD)