

# BA14EL6, Vinyl Locking Fork Terminal For 16 - 14 AWG

By Burndy  
Catalog # [BA14EL6](#)



Vinyl Locking Fork Terminal For 16 - 14 AWG

## Features

- Locking Fork Tongue design
- Allows for fast installation, screw only has to be loosened for termination
- Internal configuration of the fork prevents the terminal from coming off the screw without applying a pulling force
- Locking form is made from copper alloy and permits many installations while maintaining proper spring retention of forks

## Application

For Fast Installation And Security

## Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	Yes

## Conductor

Conductor - Copper Str Size	• 16 AWG • 14 AWG
Conductor - Copper Solid Size	• 16 AWG • 15 AWG • 14 AWG
Conductor - Copper Solid Size Range	16 AWG-14 AWG
Conductor Size	16 - 14 AWG
Conductor - Copper Str Size Range	16 AWG - 14 AWG
Conductor Type	CU C Str-Size

## Configuration

Physical Attribute - Number of Holes 1

## Connector Type

Locking Fork Terminal

## Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Pad Width inch	0.28 in
Package Height	0.000 in
Dimension - Hole Size fraction	7/50
Dimension - Hole Size inch	0.14 in
Dimension - Stud Size inch	#6
Width	0.29 in
Dimension - Z inch	0.23 in
Length	0.87 in
Dimension - Bolt Size fraction	#6
Dimension - Length Overall inch	0.87 in
Height	0.29 in
Dimensions	0.87 in x 0.29 in x 0.29 in

## General

Insulation Type	Vinyl
Trade Name	VINY LUG™
Insulation	Y
Sub Brand	VINY LUG
Physical Attribute - Tongue Type	Locking Fork
Plated	Y
Feature - Barrel Style	Shrouded
Type	BA-EL, Locking
UPC 12 Digit	781810026915
UPC 14 Digit GTIN	00781810026915
Material	Copper
Plating Type	Tin
UPC	781810026915

## Logistics

Minimum Pack Quantity	1000
Carton Quantity	1000
Pallet Quantity	99999

## Product Assets

[Catalog \[English\]](#)