



# TAOGLAS®



# Datasheet

**Part No:**  
UMB.SPA.31

**Description**

Universal Mounting Bracket for M24 Thread External Antennas

**Features:**

U-Bolt Pole Mount

Wall Mount

Hole Dimensions:  $\varnothing 31\text{mm}$

Dimensions: 161 x 144 x 157

RoHS & REACH Compliant

<b>1.</b>	<b>Introduction</b>	<b>2</b>
<b>2.</b>	<b>Specification</b>	<b>3</b>
<b>3.</b>	<b>Mechanical Drawing</b>	<b>4</b>
<b>4.</b>	<b>Packaging</b>	<b>5</b>

---

Taoglas makes no warranties based on the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and product descriptions at any time without notice. Taoglas reserves all rights to this document and the information contained herein. Reproduction, use or disclosure to third parties without express permission is strictly prohibited.



# 1. Introduction



The Taoglas UMB.SPA.31.A is a robust multi-configuration mounting bracket kit designed for pole and wall mount installation of a wide range of Taoglas External Antennas where a bracket is the preferred method of mounting the antenna. The Pantheon series can be used with this bracket allowing it to be mounted on a wall or a pole in areas where a permanent through hole mount is not feasible.

Configurations are available to suit your mounting requirements:

- U-Bolt Pole Mount
- Wall Mount

Contact your regional Taoglas customer support team for further information.


## 2. Specification

<b>Mechanical</b>	
Bracket weight	595g
Material	Brackets: Carbon Steel, Dachromate Plated. M8 Hardware: Carbon Steel, Dachromate Plated. U-Bolt Clamp: Carbon Steel, Dachromate Plated
Back mounting plate size	157 x 109 mm
Antenna mounting plate size	145 x 161.5mm
Mounting Base Large Hole	Ø31mm
Hose Clamp Pole Mount	Ø49mm min to Ø79mm max.
Wall Mount	Hole pattern; Ø8.5mm X 60.5mm center to center.
<b>Environmental</b>	
Operation Temperature	-40°C ~ +85°C
Storage Temperature	-40°C ~ +85°C




## 4. Packaging

1 Kit = 2x U-Bolts, 1x Bracket, 1x Pole mounting assist bracket, 4x wall fixtures, 4x hex nuts for U-Bolts



8pcs per Carton  
 Dimensions: 360 x 250 x 200mm



Changelog for the datasheet

**SPE-23-8-138– UMB.SPA.31**

**Revision: A (Initial Release)**

Date:	2023-09-14
Changes:	Initial Release
Changes Made by:	Jack Conroy

**Previous Revisions**




[www.taoglas.com](http://www.taoglas.com)

