Part Number : 334720707
Product Description : MX150 Mat-Sealed Female Connector Assembly, Dual Row, 6 Circuits, Keying Option C, with Connector Position Assurance, with Clipslot, Brown; For USCAR Compliance, Use Alternate Part Number: 334720716
Series Number : 33472
Status : Obsolete
Product Category : Connector Housings



Obsolete

Documents and Resources

Drawings

334720707_sd.pdf

PK-31300-903-001.pdf

Specifications

AS-33472-100-001.pdf

AS-33472-100-CH-001.pdf

AS-33472-100-FR-001.pdf

AS-33611-001-001.pdf

PS-33472-000-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant
China RoHS	Not Relevant
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Dodecamethylcyclohexasiloxane; Decamethylcyclopentasiloxane; Octamethylcyclotetrasiloxane per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS

Downloaded from Arrow.com.

- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Connector Housings
Series	33472
Description	MX150 Mat-Sealed Female Connector Assembly, Dual Row, 6 Circuits, Keying Option C, with Connector Position Assurance, with Clipslot, Brown; For USCAR Compliance, Use Alternate Part Number: 334720716
Application	Wire-to-Board, Wire-to-Wire, Automotive
Comments	with Connector Position Assurance (CPA)
Component Type	Receptacle
Product Name	MX150
UPC	883906210830

Agency

UL	E29179

Physical

Circuits (maximum)	6

Obsolete

Downloaded from Arrow.com.

Color - Resin	Brown
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	SPS/Nylon
Net Weight	10.407/g
Number of Rows	2
Packaging Type	Partitioned Carton
Panel Mount	No
Pitch - Mating Interface	3.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +150°C

Solder Process Data

Lead-Free Process Capability	N/A

Obsolete

Mates With / Use With

Mates with Part(s)

Description	Part Number
MX150 Male Connector Assembly, Bulkhead Twist-Lock, Mat-Sealed Compatible, Dual Row, 6 Circuits, Keying Option C, Dark Gray	348403430
MX150 Mat-Sealed Dual Row Male Connector Assemblies	33482

Use with Part(s)

Description	Part Number
MX150 Sealed Receptacle Cavity Plug	343454001
MX150 Female Terminals	33001
MX150 Female Terminals	33012

Downloaded from Arrow.com.

This document was generated on Sep 08, 2026

Obsolete

Downloaded from Arrow.com.