



## 2 inch pins for MR06, MR07, MR08, includes 1 pair of pins

### P/N: MR-PINS2

#### Copyright

© 2019, FLIR Systems, Inc.

All rights reserved worldwide. Names and marks appearing herein are either registered trademarks or trademarks of FLIR Systems and/or its subsidiaries. All other trademarks, trade names or company names referenced herein are used for identification only and are the property of their respective owners.

#### Document identity

Publ. No.: MR-PINS2

Commit: 55933

Language: en-US

Modified: 2019-02-25

Formatted: 2019-07-31

#### Website

<http://www.flir.com>

#### Customer support

<http://support.flir.com>

#### Disclaimer

Specifications subject to change without further notice. Camera models and accessories subject to regional market considerations. License procedures may apply. Products described herein may be subject to US Export Regulations. Please refer to [exportquestions@flir.com](mailto:exportquestions@flir.com) with any questions.



General description	
Part number	MR-PINS2
Part name	2 inch pins for MR06, MR07, MR08, includes 1 pair of pins
<p>FLIR's new insulated pins are smaller in diameter—requiring minimal force to drive the pins into a surface—resulting in less impact to the material. The sandblasted, hardened-steel pins with a single-piece design prevent bending and create an improved bonding surface for the abrasion-resistant insulation. The insulation extends all the way to the connection to the probe, so even if you drive the pins all the way into the wall cavity, the drywall will not affect the measurement.</p> <ul style="list-style-type: none"><li>• Fits FLIR's hammer, wall cavity and combo probes.</li><li>• Unibody construction rather than two piece.</li><li>• Smaller-diameter pins.</li><li>• Sandblasted hardened steel.</li><li>• Insulated with abrasion-resistant coating.</li></ul> <p>Replacement pin set for FLIR MR06, MR07, and MR08.</p>	
Meter data	
Suitable accessory	MR06, MR07, MR08
Included insulated pin pairs and length	1 pair of 2 in. (50 mm)
Warranty	<a href="https://www.flir.com/testwarranty">https://www.flir.com/testwarranty</a>
Meter physical data	
Weight	0.02 kg (0.05 lb.)
Dimensions (H × W × L)	8 mm × 8 mm × 76 mm (0.32 in. × 0.32 in. × 3 in.)
Material	Stainless steel
Color	Black insulation
Shipping information	
Packaging type	Plastic bag
Packaging contents	1 pair of 2 in. insulated pins
Packaging weight	0.0127 kg (0.03 lb.)
Packaging dimensions (H × W × L)	1 cm × 2 cm × 8 cm (0.4 in. × 0.8 in. × 3.2 in.)
Inner carton weight	1.5 kg (3.3 lb.)
Inner carton dimensions (H × W × L)	13 cm × 19 cm × 38 cm (5.2 in. × 7.5 in. × 15 in.)
Inner carton quantity (bag)	100
Master carton weight	6 kg (13.3 lb.)
Master carton dimensions (H × W × L)	28 cm × 40 cm × 40 cm (11 in. × 15.8 in. × 15.8 in.)
Master carton quantity	400





## 2 inch pins for MR06, MR07, MR08, includes 1 pair of pins

### P/N: MR-PINS2

© 2019, FLIR Systems, Inc.

#MR-PINS2; r. 55933; en-US

Shipping information	
EAN-13	0793950372029
UPC-12	793950372029
Country of origin	China
Tariff code	9025900000
Technical support	
Website	<a href="http://support.flir.com">http://support.flir.com</a>



Modified Date	Modified By
Wednesday, September 30, 2015	T&M Engineering
Description	MR-PINS2
Units	Scale
Millimeters	Not to Scale