





Color: ■ green-yellow



Dimensions in mm

Technical data	
Total number of potentials	1

Electrical data	
Rated current	20 A
Test voltage	42 V

Connection data	
Connection technology	CAGE CLAMP®
Strip length	9 ... 11 mm / 0.35 ... 0.43 inches
Clamping units	1
Solid conductor	0.08 ... 2.5 mm² / 28 ... 14 AWG
Fine-stranded conductor	0.08 ... 2.5 mm² / 28 ... 14 AWG

Physical data	
Width	8 mm / 0.315 inches
Height	15 mm / 0.591 inches
Depth	40 mm / 1.575 inches

Material data	
Color	green-yellow
Fire load	0.04 MJ
Weight	3.9 g

Commercial data		
Product Group	2 (Terminal Block Accessories)	
PU (SPU)	50 pcs	
Packaging type	Box	
Country of origin	DE	
GTIN	4045454293567	
Customs tariff number	85366990990	

Product Classification		
UNSPSC	39121421	
eCl@ss 10.0	27-44-03-13	
eCl@ss 9.0	27-44-03-13	
ETIM 9.0	EC002255	
ETIM 8.0	EC002255	
ECCN	NO US CLASSIFICATION	

Environmental Product Compliance		
CAS-No.	7439-92-1	
REACH Candidate List Substance	Lead	
RoHS Compliance Status	Compliant,With Exemption	
RoHS Exemption	6(c)	
SCIP notification number (Austria)	11a03ff5-a36f-43da-b613-56f9cc3f0f73	
SCIP notification number (Belgium)	b76949c6-e6eb-48b3-8a4f-d3e40bb5bbf3	
SCIP notification number (Bulgaria)	ba74eb32-6f43-4bff-bbdd-110f2dd35b0c	
SCIP notification number (Czech Republic)	b7e4d258-b776-4d4c-873e-0b1622a09379	
SCIP notification number (Denmark)	374f27a2-7a2f-489b-b3d3-db34ca1eeee9	
SCIP notification number (Finland)	fba41022-f292-4a5d-929b-4be4bf903756	
SCIP notification number (France)	a2e81971-2a70-4c24-8d8c-d887d2a26d87	
SCIP notification number (Germany)	534e3015-7658-4225-9766-10ffea125f7f	
SCIP notification number (Hungary)	49d347b9-f772-482a-9f27-3f50e55ac4b7	
SCIP notification number (Italy)	cf5684cb-e759-4fd2-a561-851d016e9e8f	
SCIP notification number (Netherlands)	e676c47b-5ec8-4fa4-b85c-ba063cf9c9c3	
SCIP notification number (Poland)	3fed0584-489d-4db5-ad3b-455b0e19a745	
SCIP notification number (Romania)	789bcf42-8b74-4a01-95ad-e85601b1f323	
SCIP notification number (Sweden)	a7d62418-380b-4e56-a926-5857023c5344	

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 215-911

↓



Documentation

Bid Text			
215-911	19.02.2019	xml 3.02 KB	↓
215-911	19.09.2017	doc 25.50 KB	↓


CAD/CAE-Data

CAD data
2D/3D Models 215-911
↓

CAE data
EPLAN Data Portal 215-911
↓
WSCAD Universe 215-911
↓

Installation Notes

Conductor termination



Conductor termination: Press button fully, insert stripped conductor into square entry and release.

Testing



Testing via banana plug.
Picture shows a test plug adapter (Item No. 209-170).