

D-SUB Connectors >

IP67 D-SUB Connectors >

IP67 RJ45 / USB / Fiber Optic >

Sensor Actor Line Connetors >

PCB Connectors >



Part. No.:
303W3CPXX69C60X

Short description

- Combination D-SUB
- 3W3C
- Plug

Do you have any questions?

We will be pleased to help you.



Mon-Thu. 8am - 4.30 pm

Fri 8 am - 3 pm

+49 2941 765 0

info@conec.de

[Contact form >](#)



M-F 8:30 – 5:00 ET

+919 460 8800

info@conec.com

[Contact form >](#)



M-F 8:30 – 5:00 ET

+905 790 2200

info@conec.com

[Contact form >](#)



M-F 8:30 – 5:00 ET

+0975267217

info@conec.fr

[Formulaire de contact >](#)



+0713 744 045

info@conec.pl

[Formularz kontaktowy](#)



+577 350 132

info@conec.cz

[Kontaktní formulář](#)

Please send us

☐ Quote

☐ Drawing

☐ Sample

☐ 3D File

☐ Contact me by phone

[Send request](#)

General Data

Contact type	Plug
Product type	Combination D-SUB
Size/Number of positions	3W3C

Material Data

Insulator color	Green
Insulator material	PBT GF UL 94 V-0
Material power contact	Copper alloy
Mounting option material	Copper Alloy
Plating mounting option	Nickel
Plating power contact (mating area)	Gold over nickel
Plating power contact (termination area)	Tin plated
Plating signal contact (mating area)	Gold over nickel
Shell material	Steel
Shell plating	Tin
Signal contact material	Copper alloy

Specifications

Standard IP rating	IEC 60807-2
--------------------	-------------

Technical Data

Current rating power	20 A	IEC 60807-2
Dielectric with standing voltage power	1000 V	IEC 60807-2
Dielectric with standing voltage signal	1000 V	IEC 60807-2
Extraction force	21 N	IEC 60807-2
Insertion force	21 N	IEC 60807-2
Mating cycles	50	IEC 60807-2
Power resistance standard	1 mOhm	
Quality class	Quality class 3	
Working voltage power	250 V	IEC 60807-2
Working voltage signal	250 V	IEC 60807-2

Specifications

IEC 60807-2
IEC 60807-2
IEC 60807-2
IEC 60807-2
IEC 60807-2
IEC 60807-2
IEC 60807-2
IEC 60807-2



☎ 21 663 009 30

info@conec.cn

max. working temperature

+125° C

min. working temperature

-55° C

[Contact form >](#)

Do you know our Newsletter?

- ✔ Be the first to learn about innovations concerning your connector applications.
- ✔ Newsletters every 4 to 6 weeks; unsubscribe with just one click at any time!

News FRESH

I would like to receive exclusive
product information as of now!

e-mail address

[Subscribe to our newsletter>](#)

Product areas

- D-SUB Connectors
- IP67 D-SUB Connectors
- IP67 RJ45 / USB / Fiber Optic / Power
- Bayonet
- Sensor Actor Line Connectors
- PCB Connectors
- Applications

The company CONEC

With more than 35 years of experience, CONEC has become one of the leading manufacturers in the connector industry. CONEC produces in modern production sites using high-tech technologies and reliable production processes for the application fields: industrial electronics, telecommunications, automation, automotive, aerospace and medical. High quality standards are ensured by applying DIN EN ISO 9001 standards. Depending on the product family, CONEC industrial connectors are tested and approved in accordance with UL-CSA-VDE.

Service area

- Company
- News
- Downloads
- Contact



Social Media

