SmartRack Copper Bus Grounding Bar

MODEL NUMBER: **SRGROUND**







Highlights

- Attach to rack enclosure cabinets or open frame racks to provide ground contact
- Heavy-gauge solid copper
- All hardware is included

Package Includes

- SRGROUND Copper Bus Grounding Bar
- (21) Grounding straps
- (3) Mounting buttons
- (21) M4 screws
- (21) Washers
- Owners Manual

Description

The SRGROUND is a full-length (42U) bus grounding bar made from heavy-gauge solid copper that attaches to Rack Enclosure Cabinets or Open Frame Racks to provide convenient ground contact for standard rack-mount equipment. Every other U space has a drilled and tapped hole to allow a ground wire "jumper" to be installed. The jumper then bridges to the individual pieces of equipment with grounding straps, allowing a direct path to ground, rather than going through surrounding equipment. The SRGROUND can mount in an enclosure in two ways: it can be screwed into the Rack Enclosures (hardware included) or it can be installed using the toolless mounting buttons in the Open Frame Racks.

Features

- Full length (42U) bus grounding bar made from heavy-gauge solid copper that attaches to Rack Enclosure Cabinets or Open Frame Racks to provide convenient ground contact for standard rack-mount equipment
- Every other U space has a drilled and tapped hole to allow a ground wire "jumper" to be installed
- The jumper then bridges to the individual pieces of equipment, with grounding straps, allowing a direct path to ground rather than going through surrounding equipment
- Can mount in a enclosure in two ways: it can be screwed into the Rack Enclosures (hardware included), or it can be installed using the tool less mounting buttons in the Open Frame Racks

Specifications

OVERVIEW	
UPC Code	037332154811
Accessory Type	Grounding Bars & Panels
Accessory Class	Rack Accessories
PHYSICAL	
Shipping Dimensions (hwd / in.)	2.40 x 3.60 x 78.50
Shipping Dimensions (hwd / cm)	6.10 x 9.14 x 199.39

Downloaded from Arrow.com.

Shipping Weight (lbs.)	5.50
Shipping Weight (kg)	2.49
Unit Dimensions (hwd / in.)	75.500 x 0.625 x 0.250
Unit Dimensions (hwd / cm)	191.77 x 1.59 x 0.63
Unit Weight (lbs.)	4
Unit Weight (kg)	1.81
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; EIA/ECA-310-E
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
https://tripplite.eaton.com

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Downloaded from Arrow.com.