

Part Number : 797582036
Product Description : Pre-Crimped Lead .093" Female-to-.093" Female, Tin (Sn) Plating, 300.00mm Length, 18 AWG, Black
Series Number : 79758
Status : Active
Product Category : Power and Signal Cable Assemblies

Documents and Resources

Drawings

797582036_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	79758
Description	Pre-Crimped Lead .093" Female-to-.093" Female, Tin (Sn) Plating, 300.00mm Length, 18 AWG, Black
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	.093” Crimp Terminals
Keyword	Pre-Crimped Leads
Product Name	Standard .093"
UPC	889056821094

Physical

Cable Length	300.00mm
Circuits (Loaded)	1
Circuits (maximum)	1
Color - Resin	Black
Gender	Female-Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	5.431/g
Packaging Type	Bag
Single Ended	No
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 1061
Wire Size (AWG)	18

Mates With / Use With

Downloaded from Arrow.com.

Use with Part(s)

Description	Part Number
Standard .093" Pin and Socket Dual Row Connector Housings	1261
Standard .093" Pin and Socket 3 Row Connector Housings	1292
Standard .093" Pin and Socket 3 Row Connector Housings	1360
Standard .093" Pin and Socket 3 Row Connector Housings	1375
Standard .093" Pin and Socket Single Row Connector Housings	1396
Standard .093" Pin and Socket Single Row Connector Housings	1490
Standard .093" Pin and Socket Single Row Connector Housings	1545
Standard .093" Pin and Socket Single Row Connector Housings	1619
Standard .093" Pin and Socket Dual Row Connector Housings	2163

Downloaded from Arrow.com.