



Connectors > Contacts > PCB Spring Contacts

2199248-6 ✓ ACTIVE

C-Clip Spring Contact, 1.4 mm [.055 in] High, Scalable, Side Protected, 1.6 mm [.063 in] Uncompressed Height, 3.9 mm [.154 in] Length



TE Internal #: 2199248-6
TE Internal Description: Shield Finger, Loose Piece, Type A, 1.6h

Spring Finger Type : C-Clip
Scalable : Yes
Side Protected : Yes
Uncompressed Height : 1.6 mm [.063 in]
Product Length : 3.9 mm [.154 in]

Add to List ▼

GET FREE SAMPLES



[Similar Products](#)

[Compatible Parts & Tooling](#)

- [Documents](#)
- [Features](#)
- [Product Compliance](#)

Product Drawings

CUSTOMER DRAWING FOR TYPE A SPRING FINGER

[ENG_CD_2199248_A_C-2199248_A.Pdf](#)

English

CAD Files

3D PDF

[3D_CVM_CVM_2199248-6_A3.pdf](#)

3D

Customer View Model

[ENG_CVM_CVM_2199248-6_A3.2d_dxf.zip](#)

English

[ENG_CVM_CVM_2199248-6_A3.3d_igs.zip](#)

English

[ENG_CVM_CVM_2199248-6_A3.3d_stp.zip](#)

English

We are here to help!
Get in touch with our product experts.

[CHAT WITH US](#)

[EMAIL US](#)

[CALL US](#)

Feedback

Product Specifications

Product Specification

[ENG_SS_108-115061-1_A2.pdf](#)

English

Qualification Test Report

[ENG_SS_501-115070-11_A1.pdf](#)

English

Product Change Notification


[View Product Change Notification](#)

Login required to access product change notifications

REPORT PRODUCT DATA ERROR

Compatible Parts

[Filter By Specification](#)




ASSOCIATED

2336713-2

Ultra Small - C-Clip Spring Contact, 1.15 mm [.045 in]...

From: 0.208
In-Stock

[ADD TO CART](#)



ASSOCIATED

2108611-5

Preloaded - C-Clip Spring Contact, 1.4 mm [.055 in]...

From: 0.427
In-Stock

[ADD TO CART](#)

Products with Similar Specs

[View All Similar Products](#)


THIS PRODUCT

Top Results [?](#)

PCB SPRING CONTACTS

2199248-6

C-Clip Spring Contact, 1.4 mm [.055 in] High, Scalable, Side Protected,




In-Stock

Spring Finger Type : **C-Clip**
 Scalable : **Yes**
 Side Protected : **Yes**
 Uncompressed Height : **1.6 mm**
 Product Length : **3.9 mm**

PCB SPRING CONTACTS

1565322-1

Preloaded - C-Clip Spring Contact, 1.3 mm [.051 in] High, 1.6 mm [.063




In-Stock


Spring Finger Type : **Preloaded - C-Clip**
 Scalable : **No**
 Side Protected : **No**
 Uncompressed Height : **1.6 mm**
 Product Length : **3.2 mm**

PCB SPRING CONTACTS

2108609-5

Preloaded - C-Clip Spring Contact, 2.6 mm [.102 in] High, Scalable,



In-Stock 


From **\$0.455**


Spring Finger Type : **Preloaded - C-Clip**
 Scalable : **Yes**
 Side Protected : **Yes**
 Uncompressed Height : **3 mm**
 Product Length : **2.9 mm**

PCB SPRING CONTACTS

2108614-5

Preloaded - C-Clip Spring Contact, 2.3 mm [.091 in] High, Scalable,



In-Stock 

From **\$0.534**

Spring Finger Type : **Preloaded - C-Clip**
 Scalable : **Yes**
 Side Protected : **Yes**
 Uncompressed Height : **2.7 mm**
 Product Length : **2.9 mm**


Customers Also Bought



TE Part #: **338068-4**
Board-to-Board, 4 Position,
1.27 mm [.05 in] Centerline...

\$0.934 per unit
Inventory: In-Stock

 [Add To Cart](#)



TE Part #: **640445-4**
PCB Mount Header, Vertical,
Wire-to-Board, 4 Position...

\$0.394 per unit
Inventory: In-Stock

 [Add To Cart](#)



TE Part #: **640457-6**
PCB Mount Header, Right
Angle, Wire-to-Board, 6...

[View Product](#)



TE Part #: **SQMW52R2J**
2.2 ohm, Wire Wound, Power
Resistor, 5 %, 5 W, ±300...

\$0.690 per unit
Inventory: In-Stock

 [Add To Cart](#)