




Part Number : [2130283000](#)

Product Description : CLIK-Mate 1.50mm Pitch Crimp Terminal, Male, 0.38µm Gold Plating, 26-24 AWG, Reel

Series Number : 213028

Status : Active

Product Category : Crimp Terminals



Documents and Resources

Drawings

[2130283000_sd.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[2130289200-SPK-200.pdf](#)

[5025781004-PS-000.pdf](#)


[5031491002-PS-000.pdf](#)

[5025780004-PS-000.pdf](#)

[5031490002-PS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 34; 33
China RoHS	 per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	213028
Description	CLIK-Mate 1.50mm Pitch Crimp Terminal, Male, 0.38µm Gold Plating, 26-24 AWG, Reel
Application	Signal, Wire-to-Board
Product Name	CLIK-Mate
UPC	193264238583

Electrical

Current - Maximum per Contact	2.0A
Voltage - Maximum	100V AC (RMS)/DC

Physical

Durability (mating cycles max)	30
Gender	Male
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Gold

Net Weight	38.860/mg
Packaging Type	Reel
Plating min - Mating	0.381µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.00-1.28mm
Wire Size (AWG)	24, 26
Wire Size mm ²	N/A

Mates With / Use With

Use with Part(s)

Description	Part Number
1.50mm Pitch CLIK-Mate Dual Row Plug Housings	<u>503149</u>

Application Tooling

Global

Description	Part Number
Hand Crimp Tool for 1.50mm Pitch CLIK-Mate Wire-to-Board Crimp Terminals, 28-24 AWG	<u>2002187400</u>
Extractor Tool for 1.50mm Pitch Wire-to-Board Crimp Terminal	<u>638133700</u>
FineAdjust Applicator for 1.50mm Pitch Wire-to-Board Crimp Terminals	<u>639025000</u>

Japan

Description	Part Number
S-1 Applicator for CLIK-Mate Plug Terminals, 28-24 AWG	<u>5780473700</u>