






Color: ■ gray

Similar to illustration



Dimensions in mm
 $L1 = \text{PCB length}$
 $L2 = L1 - 11 \text{ mm}$ (L2 = carrier base length)
 $L3 = L1 + 2 \text{ mm}$



DIN-rail-mount PCB carrier, size 1

DIN-rail mount PCB carrier, size 1 – carrier base, size 1; 1 m long

Note	
Note	Length calculation for a complete mounting carrier: · PCB length: L1 · Base length: L2 = L1 - 11 mm · Mounting carrier length: L3 = L1 + 2 mm · Lateral cover, size 1, 6.35 mm thick · Free space between base and PCB (when using upper PCB groove): 5 mm PCB tolerances: 1.5 mm ± 0.2 mm (thickness), ± 0.2 mm (length/width), -0.1/+0.3 for milling contours



Physical data		
Width		1000 mm / 39.37 inches
Height		71.2 mm / 2.803 inches

Mechanical data		
Mounting type		DIN-35 rail

Material data		
Color		gray
Housing material		PC/ABS

Commercial data		
Product Group		6 (INTERFACE ELECTRONIC)
PU (SPU)		1 (1) pcs
Packaging type		Box
Country of origin		DE
GTIN		4017332639484
Customs tariff number		39169010900

Product Classification		
UNSPSC		39121321
eCl@ss 10.0		27-18-27-02
eCl@ss 9.0		27-18-27-02
ETIM 9.0		EC001031
ETIM 10.0		EC001031
ECCN		NO US CLASSIFICATION

Environmental Product Compliance		
RoHS Compliance Status		Compliant, No Exemption

Downloads

Environmental Product Compliance

Compliance Search	
Environmental Product Compliance 288-600	

CAD/CAE-Data

CAD data	
2D/3D Models 288-600	

CAE data	
WSCAD Universe 288-600	
ZUKEN Portal 288-600	



1 Compatible Products

1.1 Optional Accessories

1.1.1 Installation

1.1.1.1 Mounting accessories



Item No.: 210-533
Phillips screw 2.9 x 13

1.1.1.2 Mounting carrier and mounting feet



Item No.: 288-602
Fixing foot for DIN 35 rail; gray



Item No.: 288-601
Lateral cover; Size 1; small; 6.35 mm thick; gray

1.1.2 Marking

1.1.2.1 Marking strip



Item No.: 709-196
Marking strips; for laser printer; translucent



Item No.: 709-177
Marking strips; on reel; 7.5 mm wide; not stretchable; plain; snap-on type; translucent



Item No.: 709-178
Marking strips; on reel; 7.5 mm wide; not stretchable; plain; snap-on type; white