



Chloroprene tubing and grommets H75X30BK

Helsyn H, Article number: 600-02198



Images (3)

Downloads

Features

- Highly elastic, easy to fit chloroprene tubing
- Withstands up to 120 °C intermittent temperature
- Covers many cable diameters with one size
- Available in cut lengths

Certifications & Approvals



Application

The chloroprene tubings are ideally suited to rigorous environments such as the automotive, aerospace, mass transit and defence markets.

As the material is highly elastic, it's original size can be expanded 500% on application and 200% in continuous use.

To save time and effort when fitting the tubings, try the HellermannTyton NA three prong tools and the Hellerine lubricant, which are specially designed for use with HellermannTyton chloroprene tubing.



More products in this product group

[Chloroprene tubing and grommets >](#)

Base Data

Application Tool	VA2.5/5, VA2.5/5+8, NA4/5
Colour	Black (BK)
Description Short (BMEcat) (max. 150 characters)	Chloroprene Rubber Tubing 30x7.5mm black
GLOBAL PART DESCRIPTION	H75X30BK-CR-BK
Pack Cont.	250 pcs.
Package Quantity per	bag
Product Family	Helsyn H
Product Group	Chloroprene tubing and grommets

Product Dimensions



Bundle Ø max.	13.0 mm
Inside Ø (ID)	7.5 mm
Length (L)	30.0 mm
Supplied Ø D min.	7.5 mm
Wall (WT)	1.25 mm

Material and Specifications

Elongation at break	min. 500%
ELV compliant (Article 4 - 2)	YES
Flammability	UL 94 HB
Hazardous good	No
Material	Chloroprene Rubber (CR)
Operating Temperature - °C	-65 °C to +95 °C, intermittent +120 °C
Specifications	  
Specifications	BS-4G-198 Part 1 Type 1, DEF STAN 59-15 D2

Logistics and Packaging

More Information

ETIM 5.0	EC002254
ETIM 6.0	EC002254

Further information to H75X30BK




Catalogue page
(December 2017)

 [Download >](#)




All catalogue pages

[More information >](#)



Technical drawing 15-0206-001-CSG

 [Download >](#)



Technical drawing 15-0206-002-CSG

 [Download >](#)

Competences



Heat shrink tubing


You are looking for the heat shrink tubing meeting your application requirements best? The key factors to which we owe our success are the unique and quite specific properties of our heat shrink tubing.

[Heat Shrink Tubing >](#)

Accessories



NA4/5
621-10405
Three-Pronged Pliers
for Sleeves and
Grommets



VA2.5/5 PRONG 8
621-02200
Three-pronged pliers
for sleeves and
grommets



VA2.5/5
621-00200
Three-pronged pliers
for sleeves and
grommets

Similar products



H12X20BK
600-01520
Chloroprene tubing and
grommets



H12
608-01000
Chloroprene tubing and
grommets



H12
608-01001
Chloroprene tubing and
grommets



H12
608-01003
Chloroprene tubing and
grommets



H12
608-01004
Chloroprene tubing and
grommets



H12
608-01005
Chloroprene tubing and
grommets

Show all ▾

Stay in touch with us!



Global Company

About us
Worldwide
Philosophy
Environment & Quality
Corporate Social
Responsibility
Product Development
E-Business
ACADEMY
Careers
MADE FOR REAL

Products

Product overview
Cable Ties and Fixings
Insulation
Cable Protection Systems
Electrical Installation
Identification Systems
Application Tooling
Connectivity

Competences

Cable Ties
Heat Shrink Tubing
Industrial Identification
and Self-Adhesive Labels
Cable Protection
Conduits
Electrical Installation
Electrical tape
Wire connectors
Cable rods
Downlight covers
Cable jointing
Gel-filled cable joints
Cable Tie Guns
Connectivity Products
RFID tracking
Cable tie mounts
Thermal Transfer Printer
P-Clamp
Wiring ducts
Cable clips for edges
Cable management high
temperature
applications

Markets & Industries

Automotive Industry
Solar plants
Wind turbines
Shipbuilding
Panel building
Rail industry
Food Industry
Chemical Industry
Aerospace Industry
Defence Industry

Media Centre

Videos
Product Catalogue
2018/2019
Automotive Catalogue
2016/2017
Connectivity Catalogues
2016/2017
Brochures
Software & Drivers
Helatag & Helafix
Templates
Manuals & Operating
Instructions

Events

Update: 07/10/2018

You can easily accept or reject the cookies on this site by choosing one of the following links:

[I accept cookies](#)

[I refuse cookies](#)

[Privacy](#)

Downloaded from Arrow.com

