

Home → Bits & Sets → Bit Sets → Hex Metric Insert Bit Contractor Grade 30 Pack

Hex Metric Insert Bit Contractor Grade 30 Pack



Zoom

Titles and descriptions supersede the photo. We typically use the same image for different sizes of tools.

Be the first to review this product

Filter:

SKU	Product	Size Hex Metric	Pack Quantity	Price	Qty
72582	Hex Contractor Insert Bit 2.0mm 30Pc	2.0mm	30 Bits		<input type="text" value="0"/>
72583	Hex Contractor Insert Bit 2.5mm 30Pc	2.5mm	30 Bits		<input type="text" value="0"/>
72584	Hex Contractor Insert Bit 3.0mm 30Pc	3.0mm	30 Bits		<input type="text" value="0"/>
72585	Hex Contractor Insert Bit 4.0mm 30Pc	4.0mm	30 Bits		<input type="text" value="0"/>
72586	Hex Contractor Insert Bit 5.0mm 30Pc	5.0mm	30 Bits		<input type="text" value="0"/>
72587	Hex Contractor Insert Bit 6.0mm 30Pc	6.0mm	30 Bits		<input type="text" value="0"/>

Add to Cart



Add to Wishlist



Share on Facebook



Tweet This



Pin it



We accept



Details

Wiha premium bits - exact fit precision machined
 Universal fit for all standard bit holders & power tools
 Wiha special chrome-vanadium-molybdenum tool steel
 Precision machine chamfered ends
 No cut off burrs or impact distortions
 Through hardened for best wear resistance
 Professional Quality Made By Wiha


Additional Info

Head Type	  hex metric
Country of Manufacture	Vietnam
Pack Quantity	30 Bits
Bit Drive Size	1/4" Hex
Bit Length	25mm~1"
ISO Standard Size	C6.3
Coating	Standard
Machine Hardness	HRC 59-61
Material	Impact resistant modified chrome-vanadium-molybdenum, tool steel, hardened

WRITE YOUR OWN REVIEW

Only registered users can write reviews. Please, [log in](#) or [register](#)

You may also be interested in the following product(s)



90mm Hex Metric Power Bit Single Pack

Wiha Professional Quality Hand Tools

Wiha Tools USA Since 1985

Wiha Activities In the USA Started in August of 1985 bringing Wiha quality to professional tool

Wiha Tools USA Willi Hahn Corporation

A Subsidiary of [Wiha Werkzeuge GmbH](#)



We produce Wiha products around the world under strict ISO quality standards. State of the art technology and special tool steels

assure products consistent with our reputation for outstanding performance in demanding service, repair and production applications.

[Discounts and promotions](#)

[Military Discount](#)

[IBEW-NECA Discount](#)

[Filter and sort all Wiha hand tools](#)

[Complete list of tools](#)

users in North America. Our USA warehouse and distribution center services all 50 states & Our New Facilities In Canada Supply millions of tools from stock to professional quality conscious tool users throughout North America.

[About Us](#)

[Privacy Policy](#)

[Terms and Conditions](#)

[Having technical issues with the website?](#)

We accept



[Schonach Germany](#)

**Monday - Friday Office Hours 7am - 5pm
CST USA**

1348 Dundas Cir,
Monticello, MN 55362
Customer Service Email:
cservice@wihatools.com
Tel: 763-295-6591
Fax: 763-295-6598

[Shipping](#)

[Returns](#)

[Warranty Info](#)

[About Us](#)

[Privacy Policy](#)

[Terms and Conditions](#)

**Over 5000 Professional Quality Wiha Tools
In Stock**



Newsletter [Subscribe](#)

