

**SCHROFF**

Project - 0 item(s)

MY PROJECT LIST

PRODUCTS

APPLICATIONS

INDUSTRIES

NEW PRODUCTS

CONFIGURATORS

Products ▾


Search




Home > Handle, extractor, in key form 1



Handle, extractor, in key form 1

SCHROFF

Other Views

**Catalog Number: 20817-345**[Back To Product](#)

- Handle UL 94 V-0, bearing Zn die-cast
- At 6 U, the printed board location can be offset 1 HP to the right by swapping the upper and lower handles. This creates space for SMD components on the left hand side.

Specification:

IEC 60297-3-101

Handle:

Key Form

Type:

Individual Components

Standard:

VME

Individual Component Type:

Handle

Standard pack quantity (SPQ):

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

Delivery Includes:

assembled

**Select product specifications before modifying or adding to project list or requesting a quote.**

Color-defining

Black ▾

Configuration-defining

3U Bottom / 6U Bottom ▾

[Clear Selection](#)Quantity [Add Item to Project List](#) +**Documents**

Main Catalog - Plug-in units



User manual



3 U/6 U

Links

Native CAD files


Technical Data**Qty** 1 piece (SPQ 10)**Delivery is exclusively made in Standard Pack Quantity (SPQ)**

10

Color Black**Material** Plastic Lever, die-cast zinc base, UL 94 V-0**Configuration** 3U Bottom / 6U Bottom**Delivery Comprises:**

Item	Quantity	Description
1	1	Extractor handle in key form 1, PC, UL 94 V-0
2	1	Pivot bush, Zn die-cast, nickel-plated
3	1	Socket cap head screw M2.5 × 6 with slot, St, nickel-plated

Accessories



Centre support for printed boards 6 U

21100-719

Add Item to Project List +

EXPLORE	CONTACT	DOWNLOAD
About Us Services & Capabilities News & Events Newsletter Subscriptions Strategic Partnerships Investor Relations	Customer Service Find a Sales Office or Distributor Global Locations Product Compliance & Certifications Partner Login	Download Center Reference Projects Videos Product Configurators Warranties and Terms of Sale & Procurement

© 2018 nVent. All rights reserved | [Privacy Policy](#) | [Terms of Use](#) | [Cookie Policy](#) | [Imprint](#) | [Site Map](#)

Connect With Us

