

PC Series Desktop Printers

Honeywell

Downloaded from Arrow.com.

contents

connectivity 2

media 3

power 4

summary table 6


Downloaded from Arrow.com.

connectivity

PRODUCT NAME	COMPATIBLE WITH...	SKU	DESCRIPTION
USB to Serial Adapter 	All PC Series	**203-182-100**	The USB to RS-232 adapter connects to the printer USB host (type A) port and provides serial RS-232 (female DB9) connectivity. Cable length is 1.8 m (5.9 ft). Serial flow control: XON/XOFF, RTS/CTS. (RoHS)
USB to Parallel Adapter 	All PC Series	**203-182-110**	The USB to Parallel adapter connects to the printer USB host (type A) port and provides Parallel (DB25) connectivity. Cable length is 1.8 m (5.9 ft). Operation modes: Compatibility, Nibble, Byte. (RoHS)
USB-A to USB-B Cable 	All PC Series	**321-576-004**	The USB-A to USB-B cable connects the printer device port (type B) to a PC host port (type A) to provide USB connectivity. Cable length is 2 m (6.5 ft). (RoHS) Note: This USB cable ships standard with each printer.
Wi-Fi + Bluetooth® Module 	PC23d PC43d PC43t	**203-183-420**	The user-installable Wi-Fi (802.11 b/g/n) + Bluetooth dual radio module provides both WLAN and Bluetooth connectivity. (RoHS) The Wi-Fi radio supports static (64/128 bits) and dynamic WEP, WPA, WPA2, EAP-PEAP, EAP-TTLS, LEAP, EAPFAST and EAP-TLS security protocols and is CCX version 3 compliant. The Bluetooth radio is version 2.1 + EDR, Class 2.
Ethernet Module 	PC23d PC43d PC43t	**203-183-210 (PC23d)** **203-183-410 (PC43d, PC43t)**	The user-installable Ethernet Module (IEEE 802.3) installs on the back of the printer (in place of the cover plate) and supports 10Base-T and 100Base-TX LAN communications. RJ45 CAT 5 cables up to 100 m (328 ft) in length are supported. Network Protocols Supported: TCP/IP, FTP, SNMP, LPR, HTTP.

Downloaded from Arrow.com.

media

PRODUCT NAME	COMPATIBLE WITH...	SKU	DESCRIPTION
Cutter 	PC43d PC43t	**203-184-420 (PC43d)** **203-184-520 (PC43t)**	The user-installable Cutter Module with Label Taken Sensor (LTS) is programmable for full or partial cuts. (RoHS)
Cutter Tray 	PC43d PC43t	**203-188-100**	The user-installable Cutter Tray holds up to 20 labels as they are cut. Attaches to the cutter unit.
Label Dispenser 	PC23d	**203-184-210**	The user-installable Label Dispenser Module with Label Taken Sensor (LTS) strips off the paper backing to present only the label. (RoHS)
Label Dispenser 	PC43d	**203-184-410**	The user-installable Label Dispenser Module with Label Taken Sensor (LTS) strips off the paper backing to present only the label. (RoHS)
Label Dispenser 	PC43t	**203-184-510**	The user-installable Label Dispenser Module with Label Taken Sensor (LTS) strips off the paper backing to present only the label. (RoHS)
Linerless Platen Roller 	PC43d PC43t	**203-185-400 (PC43d)** **203-185-500 (PC43t)**	The user-installable Linerless Platen Roller features a non-stick finish and dispenses printed labels when you use linerless media stock.
Platen Roller *(No picture exists for this product)*	PC42t	**50120013-001FRE (PC42t)**	This platen roller comes standard with PC42t printers.

Downloaded from Arrow.com.

PRODUCT NAME	COMPATIBLE WITH...	SKU	DESCRIPTION
Printhead 	PC23d	**201-031-220 (203 dpi)** **201-031-230 (300 dpi)**	The user-installable 203 or 300 dpi printhead can be installed on any PC23 printer. (RoHS)
Printhead 	PC42t PC43d PC43t	**50125125-001FRE (PC42t; 203 dpi)** **201-031-420 (PC43d/t; 203 dpi)** **201-031-430 (PC43d/t; 300 dpi)**	The user-installable 203 or 300 dpi printhead can be installed on any PC4x printer. (RoHS)
Media Cover Lock Bracket 	PC23d PC43d PC43t	**203-188-200**	The two-piece user installable Media Cover Lock Bracket securely attaches to the top cover and bottom case to deter media removal. It accepts a standard Number 2 lock (user supplied).

power

PRODUCT NAME	COMPATIBLE WITH...	SKU	DESCRIPTION
Power Adapter Basebay 	PC43d	**203-187-410**	The user-installable Power Adapter Basebay attaches to the base of the printer and holds the power adapter (provided with printer). (RoHS)

Downloaded from Arrow.com.

PRODUCT NAME	COMPATIBLE WITH...	SKU	DESCRIPTION
Battery Basebay 	PC43d	**203-187-420**	The user-installable Battery Basebay attaches to the base of the printer and holds the rechargeable battery (sold separately) to provide mobile printing. Must be attached to printer for charging. Uses power adapter provided with printer. (RoHS)
Rechargeable Battery Pack 	PC43d	**203-186-100**	The 2600 mAH lithium-ion Rechargeable Battery Pack installs in the Battery Basebay (sold separately) to provide mobile printing. (RoHS)
AC Power Cord 	All PC Series	**1-974028-025** **1-974027-025** **1-974029-020** **321-471-002** **586276** **321-501-002** **321-502-002** **071918** **1-974030-025**	Americas (RoHS) Europe (RoHS) UK (RoHS) Italy (RoHS) Liechtenstein and Switzerland (RoHS) Denmark (RoHS) India and South Africa (RoHS) China (RoHS) Australia (RoHS)
Power Adapter 	All PC Series	**203-186-200**	The Universal Power Adapter 100–240 V supplies power to the printer and charges the optional battery. (RoHS) Note: This Power Adapter ships standard with every printer.
Cleaning Card 	All PC Series	**1-110501-00**	The Cleaning Card accessory removes adhesives or other contaminants from the printhead and platen roller. It is suggested that a cleaning card be used with each new roll of media. One box includes 25 cleaning cards 11.43 cm x 15.24 cm (4.5 in x 6 in).

Downloaded from Arrow.com.

SUMMARY TABLE				
Models	**PC23**	**PC42t**	**PC43d**	**PC43t**
Connectivity Cables	203-182-100 (USB to Serial)	All Shown	203-182-110 (USB to Parallel)	321-576-004 (USB-A to USB-B)
Wi-Fi / BT	203-183-420	Not Available	203-183-420	
Ethernet	203-183-210	Not Available	203-183-410	203-183-410
Cutter	Not Available	Not Available	203-184-420	203-184-520
Cutter Tray	Not Available	Not Available	203-188-100	
Dispenser	203-184-210	Not Available	203-184-410	203-184-510
Linerless Platen Roller	Not Available	50120013-001FRE	203-185-400	203-185-500
Printhead	201-031-220 (203 dpi) 201-031-230 (300 dpi)	50121891-001FRE	201-031-420 (203 dpi) 201-031-430 (300 dpi) 201-031-430 (300 dpi)	
Media Cover Lock Bracket	203-188-200	Not Available	203-188-200	
Power Adapter Basebay	Not Available	Not Available	203-187-410	Not Available
Battery Basebay / Battery	Not Available	Not Available	203-187-420 203-186-100	Not Available

For more information:
www.honeywellaidc.com

Honeywell Scanning & Mobility
9680 Old Bailes Road
Fort Mill, SC 29707
800-582-4263
www.honeywell.com

Bluetooth is a trademark or registered trademark in the US and/or in other countries of the Bluetooth SIG, Inc.

PC Series Accessory Catalog Rev E 10/15
© 2015 Honeywell International Inc.

Honeywell

Downloaded from Arrow.com.