



5.0

1 Review



5.0

1 Review

 Need Help?[Browse All Products](#) | [Power Cords](#) | [Hospital-Grade Power Cords](#) | [NEMA 5-15P to IEC320C13 Power Cords](#) Roll over image to zoom in

15ft 16 AWG Hospital Grade Power Cord (NEMA 5-15P to IEC320C13) - Gray with Clear Connectors (TAA)

Replacement power cord for PCs, monitors, printers, and lab equipment; specifically crafted for the tough hospital environment!



5.0

1 Review

Product # : 48012

Connector 1 : (1) NEMA 5-15 Male

Connector 2 : (1) C13 IEC

Lengths :

15ft

2ft

6ft

8ft

10ft

12ft

266 In Stock & ready to ship! 

Add



Need it shipped today?

Place your order before the timer runs out!



21:52:43

 print  share  chat Product Info Customer Reviews Questions & Answers Distributors More Choices

Description

Certifications

Specs

Product Description

Power cords used in hospitals and other medical settings must conform to strict standards for grounding reliability, assembly integrity, strength and durability, as well as regulatory standards such as NEMA and IEC specifications. These standards are in place to ensure that power cords are safe and reliable for use in demanding hospital environments. The hospital grade power cord selection from C2G, formerly Cables To Go, offers one of the broadest selections available on the market.

From our vast selection, you'll find the right solution for replacing an overused or misplaced power cord, or to optimize office or lab layout with a cable that is the perfect length needed. This cable, from our universal C13 series collection, will work with most PCs, monitors, scanners, printers and many other devices that are powered via the industry standard 3-pin C14 connector inlet.

The female C13 connector plugs directly into the device while the male hospital grade 5-15P connector plugs into a hospital grade supply outlet. The clear connectors work with almost any environment or hospital standard. Performance is guaranteed through a lifetime warranty so performance is never an issue. Easily recognizable with the Green Dot mark, this hospital grade power cord ensures compliance and delivers maximum performance.

**WARNING:** Cancer and Reproductive Harm www.P65Warnings.ca.gov

Product Certifications



Product Specifications

Color :	Grey
Length :	15.00 Foot
UPC :	757120480129
Warranty :	Lifetime
Vendor :	C2G
Weight :	1.280 LB

- Wire Gauge and Type: SJT 16AWG x 3C
- Amp Rating: 13A
- Voltage Rating: 125V
- Jacket Diameter: 8.5mm
- UL Certified, E115330

Info

- About Us
- Order History
- Where To Buy
- More ▾

Service

- Contact Us
- OEM Solutions
- Tech Support
- More ▾

Resources

- Connector Guides
- ConnectXpress
- Drivers & Manuals
- More ▾

Have A Question?

- Get help with [Chat](#)
- Call C2G **800.506.9607**
- [f](#) [t](#) [v](#) [b](#)

