




Part Number : [1054150007](#)

Product Description : Mega-Fit Terminal Position Assurance (TPA) Retainer, 7 Circuits, 5.70mm Pitch, UL 94V-0, Glow-Wire Capable, Natural

Series Number : 105415

Status : Active

Product Category : Connector Accessories



Documents and Resources

Drawings

[1054150007_sd.pdf](#)

[1054150001-000.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[768232000-AS-000.pdf](#)

[1054171000-PS-000.pdf](#)

[1054171000-PS-CH-000.pdf](#)

[1054171000-PS-KO-000.pdf](#)


[1054171000-PS-SPA-000.pdf](#)

[1720631000-PS-000.pdf](#)

[1720631000-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC

	61249-2-21
REACH SVHC	Contains 1,1'-(Ethane-1,2-diyl)bis[pentabromobenzene] per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Accessories
Series	105415
Description	Mega-Fit Terminal Position Assurance (TPA) Retainer, 7 Circuits, 5.70mm Pitch, UL 94V-0, Glow-Wire Capable, Natural
Component Type	Terminal Position Assurance
Product Name	Mega-Fit
UPC	191130073757

Physical

Circuits (Loaded)	7
Circuits (maximum)	7
Color - Resin	Natural

Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	0.579/g
Number of Rows	1
Packaging Type	Bag
Temperature Range - Operating	-40° to +105°C, -40° to +120°C

Mates With / Use With

Use with Part(s)

Description	Part Number
Mega-Fit Free Hanging Dual Row Plug Housings	<u>105411</u>
Mega-Fit Single Row Plug Housings	<u>213814</u>
Mega-Fit Single Row Plug Housings	<u>213815</u>
Mega-Fit Dual Row Receptacle Housings	<u>171692</u>
Mega-Fit Tangless TPA-Capable Single Row Receptacle Housings	<u>200456</u>

This document was generated on Apr 11, 2026