


Shrinkable markers "Ladder Style", thermal transfer

TULT DS - 3:1 Military and Electronics



TYPE	Supplied Ø D min.	Recov. Ø d max.	Length (L)	Wall (WT)	Pack Cont.	Colour	Article-No.
TULT4.8-1.6DS-2x25WH	4.8	1.6	25.0	0.66	2,000 pcs.	White (WH)	553-71014
TULT4.8-1.6DS-2x25YE	4.8	1.6	25.0	0.66	2,000 pcs.	Yellow (YE)	553-71015
TULT4.8-1.6DS-1x50WH	4.8	1.6	50.0	0.66	1,000 pcs.	White (WH)	553-71012
TULT4.8-1.6DS-1x50YE	4.8	1.6	50.0	0.66	1,000 pcs.	Yellow (YE)	553-71013
TULT6-2DS-2x25WH	6.0	2.0	25.0	0.69	2,000 pcs.	White (WH)	553-71020
TULT6-2DS-2x25YE	6.0	2.0	25.0	0.69	2,000 pcs.	Yellow (YE)	553-71021
TULT6-2DS-1x50WH	6.0	2.0	50.0	0.69	1,000 pcs.	White (WH)	553-71018
TULT6-2DS-1x50YE	6.0	2.0	50.0	0.69	1,000 pcs.	Yellow (YE)	553-71019
TULT9-3DS-2x25WH	9.0	3.0	25.0	0.79	1,000 pcs.	White (WH)	553-71026
TULT9-3DS-2x25YE	9.0	3.0	25.0	0.79	1,000 pcs.	Yellow (YE)	553-71027
TULT9-3DS-1x50WH	9.0	3.0	50.0	0.79	500 pcs.	White (WH)	553-71024
TULT9-3DS-1x50YE	9.0	3.0	50.0	0.79	500 pcs.	Yellow (YE)	553-71025
TULT12-4DS-2x25WH	12.0	4.0	25.0	0.84	1,000 pcs.	White (WH)	553-71032
TULT12-4DS-2x25YE	12.0	4.0	25.0	0.84	1,000 pcs.	Yellow (YE)	553-71033
TULT12-4DS-1x50WH	12.0	4.0	50.0	0.84	500 pcs.	White (WH)	553-71030
TULT12-4DS-1x50YE	12.0	4.0	50.0	0.84	500 pcs.	Yellow (YE)	553-71031
TULT18-6DS-2x25WH	18.0	6.0	25.0	1.00	1,000 pcs.	White (WH)	553-71038
TULT18-6DS-2x25YE	18.0	6.0	25.0	1.00	1,000 pcs.	Yellow (YE)	553-71039
TULT18-6DS-1x50WH	18.0	6.0	50.0	1.00	500 pcs.	White (WH)	553-71036
TULT18-6DS-1x50YE	18.0	6.0	50.0	1.00	500 pcs.	Yellow (YE)	553-71037
TULT24-8DS-2x25WH	24.0	8.0	25.0	1.20	500 pcs.	White (WH)	553-71044
TULT24-8DS-2x25YE	24.0	8.0	25.0	1.20	500 pcs.	Yellow (YE)	553-71045
TULT24-8DS-1x50WH	24.0	8.0	50.0	1.20	250 pcs.	White (WH)	553-71042
TULT24-8DS-1x50YE	24.0	8.0	50.0	1.20	250 pcs.	Yellow (YE)	553-71043
TULT39-13DS-2x25WH	39.0	13.0	25.0	1.25	500 pcs.	White (WH)	553-71050
TULT39-13DS-2x25YE	39.0	13.0	25.0	1.25	500 pcs.	Yellow (YE)	553-71051
TULT39-13DS-1x50WH	39.0	13.0	50.0	1.25	250 pcs.	White (WH)	553-71048
TULT39-13DS-1x50YE	39.0	13.0	50.0	1.25	250 pcs.	Yellow (YE)	553-71049

All dimensions in mm. Subject to technical changes.
Minimum Order Quantity (MOQ) may differ from package content.



For product specific approvals and specifications please refer to the Appendix.