


2057021-1 Product Details

[Share](#) [Print](#) [Email](#)



2057021-1

TE Internal Number: 2057021-1

Active

[View 3D PDF](#)

Pluggable Connectors, Cages & Accessories

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- SFP+ Application
- Cage
- Cage Type = Single
- EMI Containment = External Springs
- Heat Sink Application = No

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Documentation & Additional Information	
<p>Product Drawings:</p> <ul style="list-style-type: none"> • SFP+ 1X1 CAGE ASSEMBLY W/ HEATSINK OPENING, SHORT SO... (PDF, English) <p>Catalog Pages/Data Sheets:</p> <ul style="list-style-type: none"> • None Available <p>Product Specifications:</p> <ul style="list-style-type: none"> • Single Port SFP+ Cages, Ganged SFP+ Cages, and SFP+ ... (PDF, English) <p>Application Specifications:</p> <ul style="list-style-type: none"> • Small Form-Factor Pluggable (SFP) Connector and Cage... (PDF, English) <p>Instruction Sheets:</p> <ul style="list-style-type: none"> • None Available <p>CAD Files: (CAD Format & Compression Information)</p> <ul style="list-style-type: none"> • 2D Drawing (DXF, Version B) • 3D Model (IGES, Version B) • 3D Model (STEP, Version B) 	<p>Related Products:</p> <ul style="list-style-type: none"> • Tooling

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)	
<p>Product Type Features:</p> <ul style="list-style-type: none"> • Product Type = Cage • Termination Type = Wave Solder <p>Mechanical Attachment:</p> <ul style="list-style-type: none"> • Configuration = Single Port • PCB Mount = Single Sided <p>Termination Features:</p> <ul style="list-style-type: none"> • Termination Post Length (mm [in]) = 2.05 [0.081] <p>Dimensions:</p> <ul style="list-style-type: none"> • Height (mm [in]) = 8.70 [0.343] <p>Body Features:</p> <ul style="list-style-type: none"> • Length (mm [in]) = 48.70 [1.917] • Width (mm [in]) = 14.50 [0.571] <p>Housing Features:</p> <ul style="list-style-type: none"> • Cage Type = Single • Cage Material = Nickel Silver 	<p>Configuration Features:</p> <ul style="list-style-type: none"> • EMI Containment = External Springs • Lightpipe = Without <p>Industry Standards:</p> <ul style="list-style-type: none"> • RoHS/ELV Compliance = RoHS compliant, ELV compliant • Lead Free Solder Processes = Reflow solder capable to 245°C, Reflow solder capable to 260°C • RoHS/ELV Compliance History = Always was RoHS compliant <p>Operation/Application:</p> <ul style="list-style-type: none"> • Application = SFP+ • Heat Sink Application = No <p>Packaging Features:</p> <ul style="list-style-type: none"> • Packaging Method = Tray <p>Other:</p> <ul style="list-style-type: none"> • Brand = Tyco Electronics

Corporate Information

- [Who We Are](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)

Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

