



Color: ■ gray

| Physical data |  |                        |
|---------------|--|------------------------|
| Width         |  | 10.5 mm / 0.413 inches |
| Height        |  | 27 mm / 1.063 inches   |
| Depth         |  | 33.4 mm / 1.315 inches |

| Mechanical data |  |                 |
|-----------------|--|-----------------|
| Mounting type   |  | Mounting flange |
| Mounting type   |  | Screw mount     |

| Material data                      |  |                                                                          |
|------------------------------------|--|--------------------------------------------------------------------------|
| Note (material data)               |  | <a href="#">Information on material specifications can be found here</a> |
| Color                              |  | gray                                                                     |
| Material group                     |  | I                                                                        |
| Insulation material (main housing) |  | Polyamide (PA66)                                                         |
| Flammability class per UL94        |  | V0                                                                       |
| Fire load                          |  | 0.051 MJ                                                                 |
| Weight                             |  | 1.9 g                                                                    |

| Commercial data       |  |                                |
|-----------------------|--|--------------------------------|
| Product Group         |  | 4 (Printed Circuit Connectors) |
| PU (SPU)              |  | 200 (50) pcs                   |
| Packaging type        |  | Box                            |
| Country of origin     |  | CH                             |
| GTIN                  |  | 4017332793476                  |
| Customs tariff number |  | 85389099990                    |



| Product Classification |                      |
|------------------------|----------------------|
| UNSPSC                 | 39121702             |
| eCl@ss 10.0            | 27-14-11-33          |
| eCl@ss 9.0             | 27-44-04-92          |
| ETIM 9.0               | EC000886             |
| ETIM 10.0              | EC000886             |
| ECCN                   | NO US CLASSIFICATION |

| Environmental Product Compliance |                        |
|----------------------------------|------------------------|
| RoHS Compliance Status           | Compliant,No Exemption |

Approvals / Certificates

General approvals



| Approval                        | Standard      | Certificate Name |
|---------------------------------|---------------|------------------|
| CSA<br>DEKRA Certification B.V. | C22.2 No. 158 | 1604421          |

Downloads

Environmental Product Compliance

| Compliance Search                           |  |
|---------------------------------------------|--|
| Environmental Product<br>Compliance 745-545 |  |

Documentation

| Additional Information |            |                   |  |
|------------------------|------------|-------------------|--|
| Technical Section      | 03.04.2019 | pdf<br>2027.26 KB |  |

CAD/CAE-Data

| CAD data             |  |
|----------------------|--|
| 2D/3D Models 745-545 |  |

| CAE data                     |  |
|------------------------------|--|
| EPLAN Data Portal<br>745-545 |  |
| ZUKEN Portal 745-545         |  |

Subject to changes. Please also observe the further product documentation!

Current addresses can be found at: [www.wago.com](https://www.wago.com)