


AP SAKK4/10 KER/WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Similar to illustration

Partition plates and end plates are essential accessories for terminal blocks. Partition plates provide optical and electrical separation of different potentials and functional groups, increasing safety and ensuring a clear structure inside the control cabinet. End plates close the terminal block row on the sides, protect against contact with live parts, and ensure a clean, stable finish. Both components are precisely matched to the respective Weidmüller terminal block series, contributing to safe, compliant, and professional wiring.

General ordering data

| | |
|------------|--|
| Version | End plate for terminals, white, Height: 40 mm, Width: 3 mm, V-0, Ceramic, Snap-on: Yes |
| Order No. | 9502630000 |
| Type | AP SAKK4/10 KER/WS |
| GTIN (EAN) | 4008 190047290 |
| Qty. | 10 items |

AP SAKK4/10 KER/WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

| | | | |
|------------|---------|-----------------|-------------|
| Depth | 37 mm | Depth (inches) | 1.4567 inch |
| Height | 40 mm | Height (inches) | 1.5748 inch |
| Width | 3 mm | Width (inches) | 0.1181 inch |
| Net weight | 12.58 g | | |

Temperatures

| | | | |
|----------------------------------|----------------|----------------------------------|-----------------|
| Storage temperature | -25 °C...55 °C | Ambient temperature | -60 °C...205 °C |
| Continuous operating temp., min. | -60 °C | Continuous operating temp., max. | 250 °C |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Material data

| | | | |
|---------------------------|---------|--------|-------|
| Basic material | Ceramic | Colour | white |
| UL 94 flammability rating | V-0 | | |

System specifications

| | |
|---------|-----------|
| Version | End plate |
|---------|-----------|

Additional technical data

| | |
|---------|-----|
| Snap-on | Yes |
|---------|-----|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000886 | ETIM 9.0 | EC000886 |
| ETIM 10.0 | EC000886 | ECLASS 14.0 | 27-25-03-01 |
| ECLASS 15.0 | 27-25-03-01 | | |